

# SP4K-12C

12,000 lumens smart cinema projector



12K  
LUMENS

4K  
4096X2160



- Brilliant image
- Ready for tomorrow, today
- Barco EcoPure™
- Fit and forget

SP4K-12C is part of the Series 4 portfolio, designed in close collaboration with industry partners. Market trends in content creation, exhibition and technology were taken into account. The result? A 4K RGB projector family, designed for cinema.

#### Brilliant image

The Series 4 brings native 4K resolution, higher contrast and enhanced uniformity into the movie theater. The Barco Active Image Management™ and its patented precision brightness technology guarantees flawless images with automatic white balances.

#### Ready for tomorrow, today

The Barco Colorgenic™ technology opens up the full P3 color space and more than 98.5% of Rec. 2020. SP4K-12C is fully enabled for future innovations like 4K 120fps and HDR images. Deliver stunning results not only on day 1, but consistently throughout the lifetime of the product.

#### Barco EcoPure™

This silent running projector (50dB(A)) is fully ready for boothless operation. In addition, the SP4K-12C smartly manages its power consumption of only 8 lm/W. In eco-mode it consumes even less than 3 Watt. What's more, remote wake up on LAN is possible for scheduled maintenance or ingest.

#### Fit and forget

The modular design of the Series 4 projectors allows for cost-effective maintenance. There are only six Barco laser plate™ spare parts to service all light source configurations. Anyone can replace the filters thanks to the toolless cover and filter handling. The SP4K-12C seamlessly integrates into your current setup.

#### Freedom of choice

The SP4K models come in many different configurations offering you the freedom of choice. A range of lumens, compatibility with both Barco lenses and selected 3rd party lenses, and optional touch displays. Play with the available options to match your specific needs.

**Product specifications****SP4K-12C****General specifications**

Native brightness	12,000 lumens (typical)
Native contrast ratio	2300:1 (typical) up to 3000:1 with HC lens
Digital MicroMirror Device™	3x 0.98" DC4K
Resolution	native 4K: 4096 x 2160
Color gamut	DCI P3 compliant (98.5% of Rec.2020; when measured in xy-color coordinates)
Light source	Laser
Prime lenses	With C-lensholder: 0.8 -1.16; 1.09 -1.40; 1.2 -1.8; 1.4 -2.05; 1.6 -2.5 ; 1.95 -3.2; 2.4 -3.9 With B-lensholder: 1.01; 1.27; 1.6 - 2.4; 1.9 - 2.6; 2.0 - 2.95; 2.3 - 3.65; 2.8 - 4.7; 3.55 - 6.95 High-brightness and High-contrast B-lenses compatible
Long-term brightness stability	40,000 hrs @ average usage conditions
Housing	integrated cooling design and patented sealed optical assembly
Dimensions (WxLxH)	Projector incl feet: 710 x 1070 x 547 mm/ 27,95 x 42,13 x 21,54 inches (710 x 1132x 547 mm/ 27,95 x 44.55x 21,54 inches with B-lensholder)
Weight	90kg / 198.5lbs
Power requirements	single phase or triple phase 200-240V 16A
Heat load (max. power)	4600 BTU/h
Exhaust airflow	300 CFM
Ambient temperature	40°C/104F Max.
Ambient humidity	85% RH max
Media server	Barco Alchemy ICP-X and other media server brands** supported.
Power consumption	1.4kW (3W in Eco mode)
Noise Level	50dB(A) @1m and 25°C ambient temperature
3D systems	Active glasses systems and polarization systems on silver screens are supported. Color separation systems are not supported.
Safety requirements	Class 1 risk group 3
User interface	Touch Display and / or web-based
Lateral lens color on edge of image	With 2K lens: 2 pixels average* With 4K lens: 1.5 pixels average* (* depends on lens, zoom, ...)
Notes	**projector configuration with ICP-D; contact Barco service for the list of supported brands

**Last updated: 05 Jul 2024**

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.