

# Soft Edge & Contrast Modulation Kit for 800, 1200,

- Improves overall light output uniformity
- Modulates red and blue videosignals to overcome color shift errors
- Improves top/bottom and left/right edge matching
- The overlapping width can be modified (0-15% of the screen width)
- Gamma correction on modulation signals
- Adjustments are frequency tracked (vertical and horizontal)
- Frequency range: 15 - 135 kHz
- Bandwidth: 60 MHz
- Second RGB analog input no longer available
- Compatible with all BARCO CRT Projectors except: BV700 series, Retro projector systems