

# Fiberlink

Adds fiber-optic technology to the solution for guaranteed quality of the final picture with a reach up to 300 meters.



**技术规格****FIBERLINK****一般规格**

范围	300 meter cascable
信号	<ul style="list-style-type: none"><li>▪ 1,5 Gig/sec</li><li>▪ no compression</li><li>▪ full quality stream to LED display</li><li>▪ Proprietary transmission</li><li>▪ error detection and correction protocol</li></ul>
室外合规性	IP 65 fiberoptic connectors

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看[www.barco.com.cn](http://www.barco.com.cn)以了解最新规格。