

# ClickShare CSC-1

Full-featured wireless presentation system for high-profile meeting rooms and boardrooms



- **Wireless connection to central screen**
- **Up to 4 users on-screen**
- **Share from laptop, tablet or smartphone**
- **Central management**
- **Delivered with 4 Buttons**

ClickShare is Barco's wireless presentation and collaboration system, that allows any meeting participant to share content on the central meeting room screen.

### **An unmatched user experience**

At the click of a button, the content of your laptop, tablet or smartphone is displayed on the large screen. The result is that all participants are involved more intensely in the decision-making process. Coupling extreme simplicity with an unmatched user experience, everybody who has used ClickShare is immediately hooked. The system's stability and ease-of-use, also drastically limits the number of needed interventions by the IT department.

### **More pixels, more content**

If you are driving two projectors, two screens, or Double HD canvas, the full-featured CSC-1 Base Unit is the right choice. This unit is fully compatible with the ClickShare Buttons and the apps for mobile devices, and was optimized for use in high-profile meeting rooms and boardrooms.

### **Optimized collaboration experience**

By enabling to display the content of up to 4 users simultaneously, the CSC-1 Base Unit brings a complete Clickshare collaboration experience. 64 Buttons can be wirelessly connected to the Base Unit, ready to share. Furthermore, perfectly synchronized sound and video ensures that movie clips can be optimally enjoyed. And dynamic content from iPads, iPhones and Samsung Galaxy devices can be shown directly to the screen using the specialized apps. For other Android devices, you are restricted to showing static content.

**Product specifications****CLICKSHARE CSC-1**

General specifications	
<b>AirPlay Support</b>	iOS mirroring (AirPlay) from iOS 9.0 up to iOS 11.3 / macOS 10.13 El Capitan
<b>Google Cast Support</b>	Google Cast not supported
<b>Operating system</b>	Windows 7/8/8.1/10 32 & 64 bit macOS 10.10/10.11/10.13 (Sierra) Android v5 & v6 & v7 (ClickShare app) iOS 11.3 & 10 (ClickShare app)
<b>Video outputs</b>	DisplayPort, Single link DVI-I VGA (via included convertor, highest resolutions only with reduced blanking) In "Dual screen" mode, connection can occur either through DVI and DisplayPort, or through VGA and DisplayPort.
<b>Frame rate</b>	Up to 30 fps (from software version V1.03.00.0001 onwards)
<b>Output resolution</b>	UHD (3840 x 2160) available from ClickShare CSC Base Unit software v01.09.00.22 onwards
<b>Noise Level</b>	Max. 28dBA
<b>Number of sources simultaneous on screen</b>	4
<b>Number of simultaneous connections</b>	64
<b>Audio</b>	Analog audio from ClickShare CSC Base Unit software  v01.02.00.09 onwards  Digital audio (embedded in DP signal) from ClickShare CSC Base Unit software v01.05.00.32 onwards
<b>iPad, iPhone and Android compatibility</b>	Available via ClickShare app for static content. For iOS devices using iOS9, full mirroring is possible from ClickShare CSC Base Unit firmware v01.09.00.22 onwards
<b>Extended desktop</b>	Available (depending on the driver of your graphics card)
<b>Authentication protocol</b>	WPA2-PSK
<b>Encryption</b>	AES CCMP
<b>Wireless transmission protocol</b>	IEEE 802.11 a/g/n
<b>Data rate wireless</b>	Up to 300Mbps
<b>Reach</b>	Max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit
<b>Frequency band</b>	2.4 GHz and 5 GHz (DFS channels not supported)
<b>Connections</b>	1x Ethernet LAN 4x (back) + 1x (front) USB Analog line out on mini jack socket (3.5mm) Analog line in on mini jack socket (3.5mm)

**Product specifications****CLICKSHARE CSC-1**

<b>Temperature range</b>	Operating: +5°C to +40°C (+41°F to +104°F) Storage: -20°C to +60°C (-4°F to +140°F)
<b>Humidity</b>	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
<b>Altitude</b>	Max 3000m (9842 ft)
<b>Lifetime</b>	MTBF = 40,000h (90% confidence level) MTBF = 100,000h (60% confidence level) MTBF conditions: <ul style="list-style-type: none"><li>■ Environment: Ground Benign</li><li>■ Temperature: 25°C</li><li>■ Method: MIL-HDBK-217F Notice 2</li></ul>
<b>Warranty</b>	3 years standard Possible to extend to 5 years
<b>System requirements</b>	PC minimum requirements: <ul style="list-style-type: none"><li>•CPU: Intel Pentium Dual Core E2140 – 2 * 1600 Mhz (or equivalent: AMD Athlon 64 X2 3800+ -2 * 2000 Mhz)</li><li>•Memory: 1024 MB RAM</li><li>•OS: Windows XP Pro/Home (SP3) (Windows Vista/7 supported, but requires more RAM)</li></ul> PC recommended requirements: <ul style="list-style-type: none"><li>•CPU: Intel Core 2 Duo E4600 – 2 * 2400 Mhz (or equivalent: AMD Athlon 64 X2 4800+ -2 * 2500 Mhz)</li><li>•Memory: 2048 MB RAM</li><li>•OS: Windows XP Pro/Home, Windows Vista, Windows 7, Windows 8</li></ul> MAC <ul style="list-style-type: none"><li>•CPU: Intel Core 2 Duo</li><li>•Memory: 2048 MB RAM</li><li>•OS: Mac OS X 10.6, 10.7, 10.8</li></ul>

**ClickShare Base Unit dimensions**

<b>Weight</b>	2.6 kg/5.75 lb
<b>Dimensions (HxWxD)</b>	181mm (incl. antennas) x 260mm x 276mm (Min.) / 7.125" (incl. antennas) x 10.236" x 10.9" (Min.)
<b>Power consumption</b>	Shutdown: 2.5W Operation (typical): 20W Maximum: 35W

Last updated: 15 Mar 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.