


# RetroGraphics 2100



## Product specifications

## RETROGRAPHICS 2100

### General specifications

Compatibility	All PAL/SECAM Video sources in progressive scan format and all NTSC Video sources, in Composite, S-VHS or RGB format All computer graphics formats : CGA, EGA, VGA, SuperVGA, XGA and S-XGA Electronic workstations with resolutions up to 1280 x 1024 pixels Most computer sources with a pixel clock < 135 MHz
Contrast	>110:1 (on 5x4 B/W checkerboard) >300:1 (full field contrast)
Light output	750 Nit / 220 ftL (full white) 530 Nit / 155 ftL ANSI
Screen size	(diagonal) 67" (1.7 m)

Last updated: 08 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.