


RetroGraphics 2100



技术规格

RETROGRAPHICS 2100

一般规格

兼容性	All PAL/SECAM Video sources in progressive scan format and all NTSC Video sources, in Composite, S-VHS or RGB format All computer graphics formats : CGA, EGA, VGA, SuperVGA, XGA and S-XGA Electronic workstations with resolutions up to 1280 x 1024 pixels Most computer sources with a pixel clock < 135 MHz
对比度	>110:1 (on 5x4 B/W checkerboard) >300:1 (full field contrast)
光输出	750 Nit / 220 ftL (full white) 530 Nit / 155 ftL ANSI
屏幕尺寸	(diagonal) 67" (1.7 m)

生成于: 08 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。