

G60-W7

7,000 lumens, WUXGA, DLP laser phosphor projector



- **Great image quality**
- **Optimal integration capabilities**
- **Guaranteed service and support**

The G60 series expands the single-chip offering with six quality projectors between 7 and 10K. It opens up the possibilities to a wider range of applications while still relying on the valued Barco service and support.

The laser light source ensures great image quality, on the one hand, but also lower maintenance compared to most lamp-based projectors on the market. Thanks to Barco's Projector Toolset software, installing and managing your projector(s) can be done from the comfort of your own computer.

The projectors are available in black and white, allowing you to choose the perfect fit for your specific environment. Their uniform compact size, the compatibility with other Barco products and the wide lens shift range enlarge the projectors flexibility.

Product specificaties**G60-W7**

General specifications	
Type projector	Single chip DLP laser phosphor projector
Resolutie	1,920 x 1,200 (WUXGA)
Helderheid	6,300 ANSI lumens 6,600 center lumens 7,000 ISO lumens
Helderheidsuniformiteit	85%
Contrastverhouding	1,200:1 sequential; 6,000:1 dynamic; Extreme black: 100,000:1
Lichtbron	Laser phosphor
Levensduur lichtbron	Up to 20,000hrs
Beeldverhouding	16:10
Oriëntatie	360° rotation, no restrictions
Verzegelde DLP™-kern	Yes
Kleurcorrectie	Yes
CLU (constante lichtuitvoer)	Yes
Trapeziumcorrectie	Yes
Beeldverwerking	Warp & blend possible via external tool
3D	Active stereoscopic 3D
Type lens	G-lenses -0.36:1 / / 0.37-0.4:1 / 0.75-0.95:1 / 0.95-1.22:1 / 1.22-1.53:1 / 1.52-2.92:1 / 2.90-5.50:1
Optische lensverschuiving	Vertical up to 100%, depending on lens Horizontal up to 30%, depending on lens Motorized zoom and focus Motorized lens shift
Ingangen	2x HDMI 1.4 / DVI-D / HDBaseT / 3G-SDI / VGA (D-Sub 15 pin) / RJ 45 Ethernet / RS232 in
Invoerresoluties	Up to 1,920 x 1,200 @ 60Hz refresh rates: 24Hz to 120Hz for 720p (1280x720) and 24Hz to 60Hz for WUXGA (1920x1200)
Softwaretools	Projector Toolset
Controle	IR, RS232, RJ45, 3.5mm phone jack for wired remote
Netwerkverbinding	10/100 Ethernet, RJ45
Voedingsvereisten	100-240V / 50-60Hz
Energieverbruik	520W nominal, 600W maximum
Stroom in stand-by	less than 0.5W
BTU/uur	1,780 BTU/h nominal; 2,050 BTU/h maximum
Geluidsniveau (standaard bij 25°C/77°F)	36dB(A) -40dB(A) depending on the used mode
Bedrijfstemperatuur	5 ~ 40 °C (sea level)
Vochtigheid in bedrijf	10 -85% RH, non-condensing
Opslagtemperatuur	-10 ~ 60 °C
Vochtigheid bij opslag	5 -90% RH, non-condensing
Afmetingen (B x L x H)	without feet: 484 x 529 x 195 mm / 19.06 x 20.83 x 7.68 in
Gewicht	without lens: 16.9 kg / 37.3 lbs
Standaardaccessoires	Power cord, wireless remote control
Certificeringen	CE, FCC Class A, cTUVUS, CCC, EAC, KCC, RCM, BIS, BSMI
Garantie	Limited 3 years parts and labor

Laatst bijgewerkt: 11 Mar 2024

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.