

# SP4K-15C

17,000 lumens smart cinema projector



17K  
LUMENS

4K  
4096X2160



- Brilliant image
- Ready for tomorrow, today
- Barco EcoPure™
- Fit and forget

SP4K-15C is part of the Series 4 portfolio, designed in close collaboration with industry partners. Market trends in content creation, exhibition and technology were taken into account. The result? A 4K RGB projector family, designed for cinema.

#### Brilliant image

The Series 4 brings native 4K resolution, higher contrast and enhanced uniformity into the movie theater. The Barco Active Image Management™ and its patented precision brightness technology guarantees flawless images with automatic white balances.

#### Ready for tomorrow, today

The Barco Colorgenic™ technology opens up the full P3 color space and more than 98.5% of Rec. 2020. SP4K-15C is fully enabled for future innovations like 4K 120fps and HDR images. Deliver stunning results not only on day 1, but consistently throughout the lifetime of the product.

#### Barco EcoPure™

This silent running projector (50dB(A)) is fully ready for boothless operation. In addition, the SP4K-15C smartly manages its power consumption of only 8.5 lm/W. In eco-mode it consumes even less than 3 Watt. What's more, remote wake up on LAN is possible for scheduled maintenance or ingest.

#### Fit and forget

The modular design of the Series 4 projectors allows for cost-effective maintenance. There are only six Barco laser plate™ spare parts to service all light source configurations. Anyone can replace the filters thanks to the toolless cover and filter handling. The SP4K-15C seamlessly integrates into your current setup.

#### Freedom of choice

The SP4K models come in many different configurations offering you the freedom of choice. A range of lumens, compatibility with both Barco lenses and selected 3rd party lenses, and optional touch displays. Play with the available options to match your specific needs.

**Product specificaties****SP4K-15C**

General specifications	
Native helderheid	17,000 lumens (typical)
Native contrastverhouding	2300:1 (typical) up to 3000:1 with HC lens
Digital MicroMirror Device™	3x 0.98" DC4K
Resolutie	native 4K: 4096 x 2160
Kleurenspectrum	DCI P3 compliant (98.5% of Rec.2020; when measured in xy-color coordinates)
Lichtbron	Laser
Primelenzen	With C-lensholder: 0.8 -1.16; 1.09 -1.40; 1.2 -1.8; 1.4 -2.05; 1.6 -2.5 ; 1.95 -3.2; 2.4 -3.9 With B-lensholder: 1.01; 1.27; 1.6 – 2.4; 1.9 – 2.6; 2.0 – 2.95; 2.3 – 3.65; 2.8 – 4.7; 3.55 – 6.95 High-brightness and High-contrast B-lenses compatible
Langdurige stabiliteit van helderheid	40,000 hrs @ average usage conditions
Behuizing	integrated cooling design and patented sealed optical assembly
Afmetingen (B x L x H)	Projector incl feet: 710 x 1070 x 547 mm/ 27,95 x 42,13 x 21,54 inches 710 x 1132x 547 mm/ 27,95 x 44.55x 21,54 inches with B-lensholder
Gewicht	105kg/231.5lbs
Voedingsvereisten	single phase or triple phase 200-240V 16A
Warmtebelasting (max. vermogen)	5700BTU/h
Luchtuitstroom	400CFM
Omgevingstemperatuur	40°C/104F Max.
Omgevingsvochtigheid	85% RH max
Mediaserver	Barco Alchemy ICMP-X and other media server brands** supported.
Energieverbruik	1.75kW (3W in Eco mode)
Geluidsniveau	50dB(A) @1m and 25°C ambient temperature
3D-systemen	Active glasses systems and polarization systems on silver screens are supported. Color separation systems are not supported.
Veiligheidsvereisten	Class 1 risk group 3
Gebruikersinterface	Touch Display and / or web-based
Laterale lenskleur op beeldrand	With 2K lens: 2 pixels average* With 4K lens: 1.5 pixels average* (* depends on lens, zoom, ...)
Opmerkingen	**projector configuration with ICP-D; contact Barco service for the list of supported brands

Laatst bijgewerkt: 09 Apr 2024

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg [www.barco.com](http://www.barco.com) voor de meest recente specificaties.