

FLDX 2.5 - 4.6 (EN64) lens

Long Zoom lens with encoders



The EN64 is an all-glass lens that is designed to optimize the image quality and performance of your projection product. The internal lens elements are carefully selected and coated to achieve the highest resolution performance and the coatings are furthermore optimized for night vision and IR transmission for training with Night Vision Goggles. The lens comes with encoders for accurate positioning of zoom, focus and iris.

Can also be used on the Barco Fx400-HR series with adapter.

Can also be used on the Barco F80-series with adapter and related software.

Product specificaties**FLDX 2.5 - 4.6 (EN64) LENS**

General specifications	
Effectieve f-getal	F 2.04-2.87 Motorized Iris F/2.04-6.0
Zoomverhouding	1,85 Motorized zoom and focus
Platformen	For Fx40, Fx70, F80 (require a lens adaptor -R98014421), F90 and Fx400 (requires a lens adapter -R9802623)
Projectieverhouding	DMD chip 4K 2.19-4.05:1 WQXGA 2.50-4.63:1 WUXGA 2.33-4.32:1 TR: Front of lens, 111.4" @6m Image size tolerance +/-2%
Brandpuntsafstand	49.52-91.6 mm
Focusbereik	Standard: 2.5m-25m (Optical)
Gewicht	3.08 kg

Laatst bijgewerkt: 04 Jul 2023

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.