

Loki

Unmistakably Barco Residential - precision engineering and manufacturing at its finest.



- Theater & Media Room Series
- 4K UHD Resolution (3,840 x 2,160)
- Laser Phosphor
- Up to 12,000 ANSI Lumens

Loki's alluring image quality is unmistakable, right from the very first encounter. Striking and assertive, his soul is a dual laser light engine, coupled to award-winning DLP technology and world-class optics.

Professional grade optics

By basing Loki's optical engine on a proven architecture, incorporating custom designed aspherical glass elements, and enhanced low dispersion glass lenses, image quality is in a class of its own. Contrast is not only increased, but the detail within the darkest parts of the image are more visible.

By basing Loki's optical engine on a proven architecture, incorporating custom designed aspherical glass elements, and enhanced low dispersion glass lenses, image quality is in a class of its own. Contrast is not only increased, but the detail within the darkest parts of the image are more visible.

State of the art electronics

Thanks to our unique single step processing technology (SSPTM), Pulse electronics are designed to process 4K UHD, HDMI 2.0a, HDCP 2.2 and HDR10 signals with extremely low latency.

Loki uses the very latest 0.9" DMD DLP chipset, to display flawless 4K UHD (3,840 x 2,160 px) images on screen.

Laser light source

Outstanding image quality requires an exceptional light source, which is why Loki uses our brand-new dual laser engine which delivers up to 12,000 ANSI lumens output.

Alongside significantly improved image uniformity, lasers last longer than traditional projector lamps, offer great image quality consistency over their lifetime, are less fragile and offer near instant on/off performance.

Liquid cooling

Loki has departed from a pure fan based cooling system, opting instead for a liquid cooling PID regulation system. This combined with our simulation grade warp engine allows Balder to operate at any angle (free rotation), offering new possibilities when it comes to architectural integration.

Product specificaties**LOKI**

General specifications	
Type projector	Single chip DLP
Technologie	0.9" DMD™
Resolutie	3,840 x 2,160 (4K UHD)
Beeldverhouding	1.78:1 (16:9)
Lichtbron	Laser phosphor
Levensduur lichtbron	20,000 - 60,000 hours Laser intensity dependent
Lichtuitvoer	DCI (P3) Color Wheel: Up to 5,700 ANSI lumens T Color Wheel: Up to 8,500 ANSI lumens M Color Wheel: Up to 12,000 ANSI lumens
CLU (constante lichtuitvoer)	Yes
Contrastverhouding	1,800:1 Sequential 450:1 ANSI
Helderheidsuniformiteit	>90%
Lensbereik	(R9802232) -EN68 (0.30:1) -Periscope Lens (requires vertical installation) (R9801832) -FLDX UST (0.41:1) -90°ns (R9802244) -EN67 (0.65:1) (R9802243) -EN66 (0.80 - 1.21:1) (R9802003) -EN76 (0.95 - 1.30:1) (R9802242) -EN63 (1.20 - 1.70:1) * (R9802241) -EN61 (1.70 - 2.50:1) * (R9801211) -EN44 (2.50 - 4.60:1) * Standard Lens Option(s)
Optische lensverschuiving	Up to 88% vertical lens shift & up to 38% horizontal lens shift (depending on lens selection) Visit the Barco Residential Lens Calculator for further information Download Lens & Airflow Data Here
Optische dowser	Yes
Kleurcorrectie	P7 RealColor™
Kleurenspectrum	DCI (P3) Color Wheel: DCI P3 T Color Wheel: REC.709 M Color Wheel: REC.709
Beeldverwerking	Embedded Warp & Blend Engine
WARP	4-Corner Warp & Bow Correction via Warp Engine
Oriëntatie	360° Rotation
Netwerkverbinding	10/100 Ethernet via RJ45 connection
Geïntegreerde webserver	Yes
Diagnose	via Prospector web interface
HDR	HDR10
3D	Active Stereoscopic 3D Additional hardware required please contact an authorized Barco representative for details
Ingangen	1 x HDMI 2.0 (HDCP 2.2) 1 x HDBaseT (HDCP 1.4 -9Gbps only) 2 x Dual Link DVI-D 2 x Display Port (1.2) 12G-SDI 1 x RJ45 Ethernet 1 x RS232 1 x Remote Control (RC) 3 x USB (2 x Rear, 1 x Front) DMX (1 x Input, 1 x Output)
Invoerresoluties	From VGA up to 4K UHD (3,840 x 2,160) @ 60Hz or up to 2,560 x 1,600 @ 120Hz
Latentie	TBD
Controle	IR, RS232, IP, 12v Trigger Driver modules available for: Crestron, Control4, RTI & Savant NOTE: 12v Trigger(s) do not follow standard functionality and require an IP command to enable / disable them. Download our integration guide for more information.
Voedingsvereisten	100 -240V / 50 -60Hz US Requires: 20A Service (NEMA 5-20P Plug Type)
Energieverbruik	2180 W -Maximum
BTU/uur	Max. 6,000 BTU/h
Stroom in stand-by	Standby ECO Mode: 110v -0.78W (with LAN Connection) 230v -0.87W (with LAN Connection)
Geluidsniveau (standaard bij 25°C/77°F)	38 dB(A)
Bedrijfstemperatuur	10 to 45 °C at Sea Level Optimal Set Point: 20 °C
Operationele vochtigheid	20 to 80% (relative humidity)

Product specificaties

LOKI

Luchtstroomvereisten	Air Inlet (from Rear w/Feet Down): Right Side Exhaust (from Rear w/Feet Down): Rear Clearance Requirements: Front: 1cm Left: 1cm Right: 50cm Rear: 100cm Top: 1cm
Luchtuitstroom	193 ft ³ /min @ 25 °C 327 m ³ /hour @ 25 °C Download Lens & Airflow Data Here
Afmetingen (B x L x H)	Excluding Lens 577 x 738 x 304 mm 22.7 x 29.1 x 12 in.
Gewicht	Excluding Lens 44.5 kg / 98.1 lbs
Verzendingsafmetingen (L x B x H)	Excluding Lens 720 x 910 x 630 mm 28.4 x 35.8 x 24.8 in.
Verzendgewicht	Excluding Lens 55 kg / 121.3 lbs
Standaardaccessoires	Power Cord, Remote Control
Certificeringen	CE, FCC Class A and cCSAus
Veiligheidsvereisten	This projector is Risk Group 2 (RG2) according to IEC EN 62471-5. This projector may become Risk Group 3 (RG3) when an interchangeable lens with throw ratio greater than 3.15 is installed. For Northern America, installation requirements according to Risk group 3 (RG3) must be followed when interchangeable lens with throw ratio greater than 2.33 is installed. Refer to the installation manual for further information.
24/7 operation	This projector is designed and warranted for heavy duty 24/7 operation. Specific measures and design considerations have been made in order for it to comply with stringent requirements in challenging applications.
Garantie	Limited 3 years parts and labor Extendable up to 5 years
*	Firmware upgradable Please contact an authorized Barco representative for details

Laatst bijgewerkt: 22 Jun 2023

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.