


OverView cPR100 (Cyclops)

100" Display Wall system integrating 3-panel Poly-Silicon LCD technology with SXGA resolution.
Includes front access and rear access.



技术规格**OVERVIEW CPR100 (CYCLOPS)****一般规格**

分辨率	SXGA
宽高比	5:4
颜色	16.7 million
灯泡	<ul style="list-style-type: none">· 120 W UHP· operation time 6,000 h (average)
电源	95-230 VAC ± 10%, 50-60 Hz
电源	300 W
亮度	650 lumens
对比度	350:1
通信	2 x D9 connectors for RS232 in/out 1 x D9 connector for Com 800 1 x Mouse Out (DIN 13) 1 x Mini-jack for wired RC 1 x IR receivers
兼容性	<ul style="list-style-type: none">· All current video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43) in composite, S-VHS, RGB or component forms· All currently proposed HDTV, extended and improved television standards (Eureka 95, Hi-vision, ACTV, IDTV, EDTV ...)· All Computer graphics formats from VGA, SVGA, XGA to SXGA· Most Macintosh computers· Workstations with a resolution up to 2,000x1,280 pixels at 76 Hz· Most sources with a pixel clock up to 200 MHz
尺寸结构	<ul style="list-style-type: none">· Diagonal 100"· Height 2843 mm / 111.93 in.· Width 1944 mm / 76.54 in.· Dept 1487 mm / 58.54 in.· Weight per unit (mechanics, screen, projector): 166 kg 366 lbs· Weight per unit of shielding and trim: 25 kg 55.1 lbs
运行环境	<ul style="list-style-type: none">· Operating temperature: 15-25°C 30-105°F· Humidity: 40-60%, non condensing depending on total wall dimensions
输入	<ul style="list-style-type: none">· Input1 x Video (BNC or cinch)1 x VGA (D15) connector3 x Stereo audio L/R (cinch)· Output1 x VGA (D15) connector1 x Stereo audio L/R (cinch)1 x Trigger Output Mini-jack
扫描频率	Horizontal: 15 kHz-115 kHz Vertical: 25 Hz-150 Hz
屏幕	<ul style="list-style-type: none">· Double Element Fresnel-Lenticular Screen, high brightness uniformity, fine pitch, vert./hor. half gain angle: 9°/32°; luminance typ. 240 cd/m²· Single Element Diffusion Screen, excellent white field uniformity vert./hor. half gain angle: 70°/70°; luminance typ. 70 cd/m²
特殊性能	Front accessible servicing area

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。