

# iCon H600

Network-centric, 1080p HD, 6,000 lumens LCD projector



## Specifiche tecniche

## ICON H600

### Specifiche generali

Emissione luminosa	6000 ANSI lumens
Risoluzione	HD 1080 (1920x1080px)
Uniformità della luminosità	> 95 % for the total screen
Rapporto di contrasto	> 800:1 (full white/full black)
Display	3 x 1.65" polysilicon LCD panel with native HDTV resolution (1920 x 1080 pixels)
Caratteristiche	<ul style="list-style-type: none"><li>Autolmage</li><li>Advanced picture-in-picture</li><li>Standard cable basket</li><li>Advanced digital zoom</li><li>Advanced Desktopintegration</li></ul>
PIP (Picture-In-Picture)	Background desktop image + up to 4 sources simultaneously (data or video)
Ingressi	Standard: <ul style="list-style-type: none"><li>Layer 1: RGBHV or Component input; Composite video input; S-Video input</li><li>Layer 2: RGBHV or Component input; Composite video input; S-Video input</li><li>Layer 3: DVI input and D15 input</li><li>Layer 4: Available for optional inputs</li></ul> Optional: The following input boards can be placed on any of the 4 layers: <ul style="list-style-type: none"><li>RGBHV or Component input; Composite video input; S-Video input</li><li>DVI input and D15 input</li><li>SDI and HDSDI input and loop trough</li></ul>
Uscite	DVI out (1920 x 1080 at 60 Hz) of full screen composed image (including window inserts)
Comunicazione	<ul style="list-style-type: none"><li>1x RS-232C (D-9 connector)</li><li>mini-jack for wired remote control</li></ul>
Compatibilità	<ul style="list-style-type: none"><li>All current video sources</li><li>All current HDTV sources</li><li>All computer graphics sources with a pixel clock up to 275 Mhz (VGA, XGA, SXGA, SXGA+, UXGA, QXGA: 2048x1536)</li><li>DVI up to UXGA and HDTV resolution</li><li>HD-SDI, SDI optionally available</li></ul>
Compatibilità sorgente ingresso	2048 x 1536 @ 56Hz max input
Dimensioni schermo	From 1-6m / 3-20ft
Frequenze di scansione	Horizontal 15KHz -110 KHz Vertical 25 Hz -150 Hz
Connessione in rete	2 x 10/100/1000 Base-T Ethernet
Server per visualizzazione integrato	<ul style="list-style-type: none"><li>Provides native 1920 x 1080 resolution</li><li>Pentium 4 2.6 Ghz, 1 Gigabyte DDR RAM, 40 Gigabyte harddisk (upgradeable)</li><li>2 x PCMCIA slot for Wireless LAN cards, memory cards, extensions for inputs and outputs, Bluetooth</li><li>2 USB connectors and PS2 connector</li><li>2 x 10/100 Mb/s Ethernet RJ 45 connector</li><li>1x RS-232C (D-9 connector)</li><li>Included software:</li></ul>
Temperatura ambiente	5°C up to 40°C
Lampada	2 x 300 Watt UHP lamp Lifetime: 1500 h/lamp
Ottiche	<ul style="list-style-type: none"><li>Fixed lenses:<ul style="list-style-type: none"><li>-OGD (0.85:1) R9840491</li><li>-OFD (1.27:1) R9840400</li><li>-OFD (2.5:1) R9840290</li><li>-OFD (7.0:1) R9840410</li></ul></li><li>Zoom lenses:<ul style="list-style-type: none"><li>-OHD (1.4 -2.0:1) R9849930</li><li>-OHD (2.1 -3.0:1) R9849810</li><li>-OFD (3.4 -4.5:1) R9840060</li><li>-OFD (4.5 -6.0:1) R9840100</li></ul></li></ul>
Spostamento obiettivo	Vertical: -120% to +120% Horizontal: -50% to +50%
Filtri polvere	Dense High Quality Microfilter (front side removeable)
Livello di rumore	< 39 dB
Tensione di alimentazione	90V-255V
Consumo energetico	Max. 900 Watt
Dissipazione alimentazione	Max. 2900 BTU/hour
Alimentazione CA	90V-255V (50 Hz -60Hz)
Peso	35 kg (77 lbs)
Dimensioni:	D x W x H, without cable basket: 679 x 567 x 282 mm (26.73 x 22.32 x 11.10 inch)
Norme di sicurezza	Compliant with UL1950 and EN60950
Interferenza elettromagnetica	Compliant with FCC rules & regulations, part 15 Class A, CE EN55022 Class A and CCC

Generato il: 09 Jul 2024

© 2024 Barco nv. Tutti i diritti riservati. La riproduzione totale o parziale è proibita in assenza di autorizzazione scritta. Tutti i nomi di marchi e di prodotti sono marchi, marchi registrati o nomi commerciali dei rispettivi proprietari. A causa delle continue innovazioni, le informazioni e le specifiche tecniche sono soggette a modifiche senza preavviso. Controlla [www.barco.com](http://www.barco.com) per le specifiche più recenti.