

ClickShare Bar Core

Video bar for engaging, effortless wireless conferencing



- **Crystal-clear, high-quality stereo audio***
- **Advanced AI-powered 4K camera**
- **Simplified installation**
- **Sound investment: fewer interventions, minimized downtime, future-proof platform**
- **Carbon-neutral product****

ClickShare Bar Core is a carbon-neutral, all-in-one video bar that enables engaging, effortless wireless conferencing in small and medium-sized meeting rooms with any videoconferencing platform. This solution ensures meeting participants feel heard and seen thanks to its high-quality AV capabilities while offering simplified installation and reduced Total Cost of Ownership.* Stereo speakers will be available mid 2024.**Carbon-neutral label targeted for end Q1 2024.

Product specifications

CLICKSHARE BAR CORE

| General specifications | |
|--------------------------------------|---|
| Operating system | Windows 10 and higher macOS 11 (Ventura) and higher Android v13 and higher (ClickShare App) iOS 16 and higher (ClickShare App) |
| System requirements | For a smooth experience with Microsoft Teams or Zoom Minimum: Intel i3 dual-core processor / 8GB RAM / OS: Windows 10 latest build or Mac OS Ventura latest build Recommended: Intel i5 4-core processor / 8GB RAM / OS: Windows 11 latest build or Mac OS latest build |
| Video outputs | 4K UHD (3840*2160) @ 30Hz. HDMI 1.4b or USB-C DP ALT mode (DisplayPort 1.2) |
| Video inputs | - |
| Camera | 4K camera, 3x zoom/ePTZ, 120°FOV |
| Camera AI | Group framing and composition mode with up to 4 people |
| Audio output | 2x 10W full duplex and stereo speakers, 8 Ohms impedance (available mid 2024) |
| Audio pickup | 6 beamforming MEMS microphones with echo and background noise cancellation. Pickup range up to 15 feet / 4.5 meters |
| ClickShare Buttons | 1 |
| ClickShare App | Desktop & Mobile |
| Native protocols | Airplay, Google Cast, Miracast (available mid 2024) |
| Noise Level | Fanless |
| Authentication protocol | WPA2-PSK in stand-alone mode WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode |
| Wireless transmission protocol | IEEE 802.11 a/g/n/ac and IEEE 802.15.1 |
| Reach | Max. 30m (100 ft) between ClickShare Button and ClickShare Bar |
| Frequency band | 2.4 GHz and 5 GHz (DFS channels supported in select number of countries in network integration mode) |
| Connections | 1x USB-C 3.1 (DP) to screen, 1x USB-A 2.0, 1x Ethernet LAN 1Gbit, 1x USB-C 2.0 (side) |
| Temperature range | Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F) |
| Humidity | Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing |
| Anti-theft system | Kensington lock (back and bottom) |
| Certifications | FCC/CE |
| Touch screen support & Interactivity | No |
| Wireless conferencing | via App or Button |
| Local view | Yes |
| Network connection | LAN & WiFi |
| Management and reporting | Yes |
| Warranty | 1 year standard. 5 years coverage upon registering via SmartCare |
| ClickShare Base Unit dimensions | |
| Dimensions (HxWxD) | 98 mm x 640 mm x 101 mm |
| Power consumption | Operational: 5-20W, 65W Max |
| Power supply | Standard 110/220 V AC plug or USB-C (back) |
| Weight | 2500 gr |

Last updated: 12 Apr 2024

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.