

Consul

Compact, Dual Screen, L-Shaped Projection Table



- Super-flexible IR emitter holders enable orientation of the emitter's optimal reception of the IR synchronization signal.
- Dedicated space for storage of VR accessories such as active glasses.
- Pop-up shelf for support of VR peripherals and accessories.

技术规格**CONSUL****一般规格**

兼容性	Compatible with all sources from Video up to 1600 x 1200 pixel resolution workstations
可选	Standard green phosphor tube for non-stereoscopic projection Built-in electromagnetic protected loudspeakers
扫描频率	Horizontal: 15 -110 kHz autolock Vertical: 37 -200 Hz autolock
屏幕尺寸	Size: 2x 67"(2 x 1,7 m) diagonal DAB(Diffuse and Bright) screen

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。