

D320



Product specifications**D320****General specifications**

Input	4 user defined inputs Front accessible Integrated video processing Auto sensing, hot swappable S-video, composite, YUV, RGB SDI, HD-SDI, DVI up to UXGA
Compatibility	LED displays
Output	DVI-A, DVI-D, RGB
Control	<ul style="list-style-type: none">- Scaler4 input channels [Data-Video] fully scalable to desired output resolution- Z-order Instant modification of Z-order control, for each output window- Window positioning Intuitive positioning interface- Connectors RS 232 [RJ11]
Effects	Anamorphic imaging Chroma-keying [per input] Alpha-keying [per input] Z-order control Windowing/ View ports
Operating T°	0° <-> 45°
Power	240W-480W auto ranging 90-264V (50-60 Hz) Connector: 3 pin IEC
Order Information	R9851570

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.