

BarcoGraphics 4000



- Three 1.3" poly-silicon LCD panels with Micro Lens Arrays (MLA) and a resolution of 1024 x 768 pixels
- A unique dual-lamp system with two 160 Watt UHM lamps
- A Digital Gamma Correction circuitry
- Compatible with all sources from VHS Video to HDTV and improved TV-standards to all computer graphics formats and electronic workstations up to 1280 x 1024 pixels
- Indicators for lamp errors, thermal warnings and suggested replacement
- User-adjustable automatic stand from 1-60 minutes
- Powersave function
- A wide range of inputs
- Auto-Image
- Picture-in-Picture

技術仕様

BARCOGRAPHICS 4000

一般仕様	
光出力	2,200 ANSI lumen
LCD パネル	3 active matrix 1.3" poly-silicon LCD panels with Micro Lens Arrays and a resolution of 1024 x 768 pixels (XGA)
互換性	Compatible with: All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats Digital Video formats: HDTV, 720p and 480p All computer graphics formats from VGA, S-VGA, XGA to S-XGA Electronic workstations with a resolution up to 1280 x 1024 pixels
コントラスト	>200:1 (full white/full black)
ランプ	Dual-lamp technology with 160 Watt UHM DC lamps with a typical lifetime of 2,000 hours
対応スクリーンサイズ	0.6 -6 m / 1.8 -20 ft.
重量	9.2 kg / 20.3 lbs.

生成日:09 Jul 2024

© 2024 Barco nv.(C) Barco. All rights reserved. (無断転載を禁ず。) 書面による許可なく全部または一部を複製することは禁止されています。すべてのブランド名および製品名は、それぞれの所有者の商標、登録商標、または商号です。継続的な技術革新により、情報および技術仕様は予告なく変更される場合があります。最新の仕様についてはwww.barco.comをご確認ください。

