

RLM-W6

6,000 lumens, WUXGA, 3-chip DLP projector



In meeting rooms and boardrooms, the RLM-W6's WUXGA (1920x1200) resolution makes sure you and your colleagues see all important details at once. With the WUXGA resolution, you can show full HD video content and banners, tickers or subtitles at the same time. In your company's lobbies and entrance hall, with the RLM-W6's three-chip DLP color quality, your brand is depicted just the way you want it. For auditoriums and similar large rooms, Barco's RLM-W6 offers a light output of 6,000 lumens, which means that from the first to the last row, presentations will be clearly visible.

Green and ergonomic

The RLM-W6 consumes 33% less power than comparable projectors and is 10 times as silent as its nearest competitors. It removes the strain of working under a constant drone of projection equipment, and makes the only noticeable thing about it its image quality.

With the RLM Commander software, handling the RLM-W6 is easy. Barco's free Projector Toolset software is also compatible with the RLM-W6. This means that if you already have other Barco projectors in your AV network, our free and user-friendly software can manage them all at the same time.

Product specificaties**RLM-W6****General specifications**

Type projector	WUXGA 3-chip DLP digital projector
Technologie	0.67" DMD™ x3
Resolutie	1,920 x 1,200
Helderheid	6,300 center lumens / 6,000 ANSI lumens*
Contrastverhouding	2,200:1 (standard) / 3,000:1 (CE)
Helderheidsuniformiteit	95%
Beeldverhouding	16:10
ScenergiX	N/A
Type lens	RLDW
Lenzen	(fix) 0.77:1 ; 1.16:1 ; (zoom) 1.45-1.74 ; 1.74-2.17 ; 2.17-2.9 ; 2.9-4.34 ; 4.34-6.76
Optische lensverschuiving	Vertical: -100% to +100% / Horizontal: -35% to +35% on zoom lenses
Kleurcorrectie	P7
Lampen	2x280W
Levensduur lamp	1,500 hours (typical) / 2,000 hours (maximum)
Transport met lamp	Yes
Lampbehuizing, snelle vervanging	Yes, auto lamp select
Lampgarantie (vervanging op locatie/in de fabriek)	120 days, 500 hours
Verzegelde DLP™-kern	Standard
Picture-in-Picture	Up to two sources simultaneously
Oriëntatie	table -ceiling -side (portrait)* -vertical * lamp door down/bottom
WARP	H+V keystone
Geïntegreerde webserver	Yes
3D	Passive circular polarized (optional)
Ingangen	2 x HDMI (HDCP 1.3); 5-BNC (RGBHV, RGBS/RGBsB;YUV); VGA (RGBHV, RGBS/RGBsB; YUV); cinch (RGBs, YUV); Composite video; S-Video
Invoerresoluties	From NTSC up to UXGA (1600x1200), including WUXGA (1920x1200)
Max. pixelklok	165 MHz
Softwaretools	Projector Toolset
Controle	Mini-jack + IR, RS232, 12v trigger
Netwerkverbinding	10/100 base-T, RJ-45 connection
Voedingsvereisten	90-240V / 50-60Hz
Max. energieverbruik	700W / Standby mode:
Geluidsniveau (standaard bij 25°C/77°F)	37dB(A)
Operationele omgevingstemperatuur	0-40°C / 32°-104°F
Operationele vochtigheid	0-80% (non condens)
Dissipatie BTU	max 2388 BTU/h
Afmetingen (B x L x H)	500 x 669.74 x 247mm / 19.69 x 26.36 x 9.72 inches
Gewicht	26kg (57.3lbs)
Verzendingsafmetingen	(LxWxH) 820 x 660 x 380mm / 32.28 x 25.98 x 14.96 inches
Verzendgewicht af fabriek	30kg (66.1lbs)
Standaardaccessoires	Power cord, wireless remote control
Certificeringen	Compliant with FCC rules and regulations, part 15 Class A and CE EN55022 Class A, CE, TUV, RoHS, WEEE
Garantie	3 years standard, 4th or 5th year optional
*	+/-10%

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.