


# Spare lamp for XLM HD30



**Product specifications****SPARE LAMP FOR XLM HD30****General specifications**

Power	6.3 kW
-------	--------

**Last updated: 15 Mar 2023**

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.