


Spare lamp for XLM HD30



Product specifications

SPARE LAMP FOR XLM HD30

General specifications

| | |
|-------|--------|
| Power | 6.3 kW |
|-------|--------|

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.

