

ClickShare Bar Core

Video bar for engaging, effortless wireless conferencing



- **Crystal-clear, high-quality stereo audio**
- **Advanced AI-powered 4K camera**
- **Simplified installation**
- **Sound investment: fewer interventions, minimized downtime, future-proof platform**
- **Carbon-neutral product**

ClickShare Bar Core is a carbon-neutral, all-in-one video bar that enables engaging, effortless wireless conferencing in small and medium-sized meeting rooms with any videoconferencing platform. This solution ensures meeting participants feel heard and seen thanks to its high-quality AV capabilities while offering simplified installation and reduced Total Cost of Ownership.

Product specifications

CLICKSHARE BAR CORE

General specifications

Operating system	Windows 10 and higher macOS 11 (Ventura) and higher Android v13 and higher (ClickShare App) iOS 16 and higher (ClickShare App)
System requirements	For a smooth experience with Microsoft Teams or Zoom Minimum: Intel i3 dual-core processor or AMD Ryzen 7 / 8GB RAM / OS: Windows 10 latest build or Mac OS Mojave latest build Recommended: Intel i5 4-core processor or AMD Ryzen 9 / 8GB RAM / OS: Windows 11 latest build or Mac OS latest build
Video outputs	4K UHD (3840*2160) @ 30Hz. HDMI™ 1.4b or USB-C DP ALT mode (DisplayPort 1.2)
Video inputs	-
Camera	4K camera, 3x zoom/ePTZ, 120°FOV
Camera AI	Group framing and composition mode with up to 4 people
Audio output	2x 10W full duplex and stereo speakers, 8 Ohms impedance (available mid 2024)
Audio pickup	6 beamforming MEMS microphones with echo and background noise cancellation. Pickup range up to 15 feet / 4.5 meters
ClickShare Buttons	1
ClickShare App	Desktop & Mobile
Native protocols	Airplay, Google Cast, Miracast (available mid 2024)
Maximum sources simultaneously on screen	1
Noise Level	Fanless
Authentication protocol	WPA2-PSK in stand-alone mode WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode
Wireless transmission protocol	IEEE 802.11 a/g/n/ac and IEEE 802.15.1
Reach	Max. 30m (100 ft) between ClickShare Button and ClickShare Bar
Frequency band	2.4 GHz and 5 GHz (DFS channels supported in select number of countries in network integration mode)
Connections	1x USB-C 3.1 (DP) to screen, 1x USB-A 2.0, 1x Ethernet LAN 1Gbit, 1x USB-C 2.0 (side)
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock (back and bottom)
Certifications	FCC/CE
Touch screen support & Interactivity	No
Wireless conferencing	via App or Button
Local view	Yes
Network connection	LAN & WiFi
Management and reporting	Yes
Warranty	1 year standard. 5 years coverage upon registering via SmartCare
ClickShare Base Unit dimensions	
Dimensions (HxWxD)	98 mm x 640 mm x 101 mm
Power consumption	Operational: 5-20W, 65W Max
Power supply	Standard 110/220 V AC plug or USB-C (back)
Weight	2500 gr

Last updated: 02 Oct 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.