

# MD(1.2:1) Lens



**Product specifications****MD(1.2:1) LENS****General specifications**

|                          |                                    |
|--------------------------|------------------------------------|
| Distortion               | < 0.5%                             |
| EFL                      | 80 mm / 3.15"                      |
| Length                   | 248 mm / 9.75"                     |
| Lens Aperture            | F / 4.6                            |
| Max Diameter             | 125 mm / 4.9"                      |
| Net Weight Dimensions    | 3.08 kg / 6.8 lbs                  |
| Projection Distance      | 1.3 -12 m / 52 -481"               |
| Relative Luminance       | 75%                                |
| Resolution               | MTF > 70%<br>@ 7 lp / mm 18 lp / ° |
| Screen Width (min / max) | 1 -10 m / 40 -400"                 |
| Throw Ratio              | 1.2                                |

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.