

# Barco C-Series - LLU Kit

Laser Light Upgrade with RGB+ technology



- Instant laser upgrade
- One-to-one form fit in Barco Series 2
- Exceptional Image Quality
- Highest lumens/watt offer on the market

The Laser Light Upgrade kit (LLU) allows you to upgrade any Barco Series 2 xenon projector to laser in as little as 4 hours. In other words, you can benefit from the advantages of laser in no time at all with minimal investment.

### One-to-one form fit with Barco Series 2

Thanks to its fit for purpose design, the entire projector – not just the light source – is manufacturer certified and complies with all safety standards. This approach allows Barco to respect the current warranty and even unlocks the option to extend the warranty on the complete projector up to 13 years.

### Exceptional Image Quality

This unprecedented combination of two worlds generates an amazing color space compliant with DCI P3, and wide color gamut ready. The RGB+ laser light source generates up to 30% more brightness compared to the original Xenon specification, with up to 20% more contrast.

### Highest lumens/watt offer on the market

The solution is capable of generating an unmatched 12 lumens per watt. This results in the biggest reduction on the market in both optical and thermal power consumption, for up to 70% savings per year.

**Product specifications****BARCO C-SERIES - LLU KIT****Ogólne specyfikacje**

Jasność	LLU DP2K-12C+ :12,000 lumens* LLU DP2K-15C+ :15,000 lumens* LLU DP2K-20C+ :20,000 lumens*
Soczewki stałooogniskowe	R9855957 -2K/4K 0.98" 1.2-1.81 R9855931 -2K/4K 0.98" 1.4-2.05 R9855932 -2K/4K 0.98" 1.6-2.5 R9855934 -2K/4K 0.98" 1.95-3.2 R9855936 -2K/4K 0.98" 2.4-3.9
Długość terminowa stabilności jasności	30,000hrs @ average usage conditions
Wymiary (szer. x wys. x gł.)	524.5 x 309 x 332 mm / 20.6 x 12.1 x 13.1 inches
Waga	10.8 kg / 23.8 lbs
Wymagania dotyczące zasilania	LLU DP2K-12C+ : 12A @ 200-240V (50-60Hz) LLU DP2K-15C+ : 12A @ 200-240V (50-60Hz) LLU DP2K-20C+ : 15A @ 200-240V (50-60Hz)
Temperatura otoczenia	Max. 35°C or 95°F (projector and cooler)
Wilgotność otoczenia	Max. 85 % (projector and cooler)
Zużycie energii	12 lumens/watt
Systemy 3D	Active glasses systems and polarization systems on silver screens are supported. Color separation systems (Dolby 3D and 6P) are not supported.
Wymagania bezpieczeństwa	Show safety: the customer shall take precaution for the laser safety (respect the hazard distance and separation height) according to local laser show safety regulations. Workplace safety: the customer shall take precaution for: <ul style="list-style-type: none"><li>• workplace safety as prescribed by the local authorities</li><li>• basic laser safety training for operators</li><li>• laser safety program implementation in the company;</li><li>• access limitation only to trained personnel: area labelling, etc.</li></ul> GB 4943.1, IEC60825, IEC/EN62471, IEC/EN/UL60950-1, EU/China ROHS, REACH, WEEE
*	Actual brightness out of projector may vary based on projector condition / optical losses

**Last updated: 03 Oct 2024**

© 2024 Barco nv. Wszelkie prawa zastrzeżone. Powielanie w całości lub w części bez pisemnej zgody jest zabronione. Wszystkie nazwy marek i produktów są znakami towarowymi, zastrzeżonymi znakami towarowymi lub nazwami handlowymi odpowiednich właścicieli. Ze względu na ciągłe innowacje, informacje i specyfikacje techniczne mogą ulec zmianie bez wcześniejszego powiadomienia. Sprawdź [www.barco.com](http://www.barco.com), aby uzyskać najnowsze specyfikacje.

[www.barco.com](http://www.barco.com)