


# C8

8.33mm pixel pitch, 5,000 nits outdoor LED display



- **Suited for cross-rental applications**
- **Slim design for easy integration**
- **Hermetically sealed and fanless design**
- **Simple control**

The C8 outdoor LED display is a member of Barco's renowned C-series family and shares its mechanics such as truss beams, feet and stacking frames with the other C-series LED displays. The electronic backbone of the C8 is identical to that of the renowned C5 display, powered by the DX image processor and controlled by the Director Toolset software.

#### **Perfectly suited for cross-rental applications**

As the C8 is based on high-quality LEDs with narrow binning, and the calibration is done on the Barco proprietary calibration carousels, it is perfectly suited for cross-rental applications. This not only guarantees consistent brightness, it also offers rental companies the flexibility to combine LED tiles from different batches. Thanks to its slim design, the C8 can also easily be integrated in the most challenging setups. What's more, the display comes with clickable shaders that can simply be replaced in case of damage.

#### **Ultimate image quality**

The versatile C8 offers high-quality scaling, an unlimited pixel count (through stacking of multiple processors), auto redundancy and 16-bit processing per color. Another significant feature is its hermetically sealed and fanless design which guarantees crisp images at all times.

#### **Simple control**

The C8 LED display can easily be controlled by the remote management software. What's more, thanks to the optional light sensors and intelligent management services, the display adjusts its brightness automatically.

#### **Typhoon tested**

The C8 outdoor LED display meets Barco's typhoon 24/7 test standards. In the 'typhoon test' not only the effect of water and dust (the basis for IP rating) is tested but also the impact of UV rays, varying temperatures and vibrations is taken into account. The 'typhoon tested' quality label guarantees a reliable product that can withstand the most severe weather conditions.

**Product specifications****C8****General specifications**

Pixel pitch	8.33 mm
Brightness	5,000 nits
LED type	3-in-1 SMD
Processing	16 bit/color
Colors	281 trillion
Refresh rate	3,200 Hz
Hor. viewing angle	120° @50% brightness
Vert. viewing angle	-60°/+50° @50% brightness
Contrast ratio	2,600:1
Shaders	Clickable (replaceable without tools)
Lifetime	100,000 hours @ 50% brightness
Avg Power Consumption	220 W/m <sup>2</sup> (max 660 W/m <sup>2</sup> )
Operation power voltage	200-240 V / 50-60 Hz
Tile size (WxHxD) in mm	400 x 400 x 68 mm
Weight	7 kg/tile 44 kg/m <sup>2</sup>
Pixel density	14,400/sqm 1,338/sqf 2,304/tile
Curve capability	Through replaceable dowels (standard dowels: radius +4m / +8m / -7.5m / -10m / -22m)
Typhoon rating	Typhoon 24/7
IP rating	IP65
Max. stacking	12 tiles (with Barco foot mechanics)
Max. hanging	25 tiles
Source compatibility (with digitizer)	CVBS, YC, YUV, RGB, DVI (single and dual link, up to 2048 x 1536), SDI, HDSDI, Dual link HDSDI
3D capability	Yes (L/R separate, side by side, 120 Hz)
Interfaces/Ports	x2 HDMI link
Link interface	NNI interface (HDMI connector)
Max link length	3 m (via Barco HDMI cable) 300 m (via Barco fiber solution)
Max power cascade connection	20 tiles
Temperature range	0°C / +45°C (operational) -20°C / +60°C (storage)
Humidity	10% / 99% (operational) 10% / 99% (storage)
Certifications	CE, ETL/UL, FCC Class B, WEEE

Last updated: 10 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.