


STEALTH™

<P>Transparent, modular and cost-effective LED display</P>



Product specifications**STEALTH™****General specifications**

Pixel pitch	25 mm
Color depth	48-bit/pixel
Light output	2,400 nits (average), 3,600 nits (max)
Transparency	60% (aperture ratio)
Panel color	Black or white
Power consumption	70W/panel
Dimensions	Length: 398.5 mm (15.69 in.) Width: 38.5 mm (1.52 in.) Height: 400.0 mm (15.75 in.)
Weight	1.0 kg (2.20 lbs.)

Last updated: 10 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.