

# BarcoGraphics 6300



- High light output of 2,200 ANSI lumen
- Native panel resolution of 1,024 x 768 pixels
- Vibrant images with remarkable depth and clarity
- Perfect geometry
- Razor sharp in every corner
- Exceptional input compatibility
- Impressive array of input connections
- Easy picture alignment through BARCO's AutoImage feature
- Direct stacking
- Motorized zoom, focus and lens shift
- Precise projection from any position or distance
- Easy replacement for older generation projectors

**기술 사양****BARCOGRAPHICS 6300****일반 사양**

광 출력	2200 ANSI Lumen
LCD 패널	3 active matrix poly-silicon LCD panels (1.8" diagonal) with a resolution of 1,024 x 768 pixels (aspect ratio 4:3)
호환성	All current Video sources in Composite, S-VHS, RGB or Component forms All currently proposed HDTV, extended and improved television standards All computer graphics formats from VGA, S-VGA, XGA to S-XGA Most Macintosh computers Electronic workstations with a resolution up to 1280 x 1024 pixels/60 Hz Most sources with a pixel clock up to 135 MHz
명암비	>350:1 (full white/full black)
램프	400 Watt metal-halide arc lamp with a typical lifetime of 750 hours
스크린 크기	For the zoom lenses : 1 -6 m For the 0.8 lens: 1 -1.7 m
무게	Body only: 17.7 kg / 39.0 lbs. Body + lens: 21 -25 kg / 46.3 -55.1 lbs.

**작성일: 09 Jul 2024**

© 2024 Barco nv. All rights reserved. 서면 허가 없이 전체 또는 부분을 복제하는 것은 금지됩니다. 모든 브랜드명 및 제품명은 상표, 등록 상표 또는 해당 소유자의 상표입니다. 지속적인 혁신으로 인해 정보 및 기술 사양은 사전 고지 없이 변경될 수 있습니다. 최신 사양은 [www.barco.com](http://www.barco.com)을(를) 확인하세요.