

# TF-20

All conditions, outdoor 20mm LED tile



LOW ENERGY



WATERPROOF



CONTRAST



PIXEL PITCH



## 技术规格

## TF-20

### 一般规格

像素间距	20.0 mm
亮度	6,000 nits
LED配置	3x lamp
LED密度	7,513/m <sup>2</sup>
水平观察角度	110° (min 50% brightness)
垂直视角	+15, -45° (min 50% brightness)
对比度	4,000:1 (at 500 lux)
寿命	100,000 hours to 50% of initial brightness
功率消耗	400W/tile (max) 120W average
操作电压	200-240V / 50-60Hz
瓦状尺寸	Width: 960mm Height: 960mm Depth: 282mm
瓦状尺寸	Width: 960mm Height: 960mm Depth: 282mm
瓦状尺寸	Width: 960mm Height: 960mm Depth: 282mm
瓦状尺寸	Width: 960mm Height: 960mm Depth: 282mm
重量 / 层数	48 kg
IP等级	IP65/54
处理	16 bit/color
颜色	281 trillion
刷新率	800Hz
连接界面	DVI interface (DVI connector)
更大导线长度	4.5m (with Barco DVI cable)
界面	2x DVI
更大串联	6 tiles
可维护性	Front and back (tools required for front)
工作温度	-35 -50°C
存储温度	-35 -50°C
工作湿度	10-99%
存储湿度	10-99%
信号源兼容性	CVBS, YC, YUV, RGB, DVI, SDI, HDS DI (DX-700: and Dual link DVI, Dual link HDS DI)
可操作数字转换器	DX-700 (with DVI output card), D320, LEDPRO
认证	ETL, CE, FCC, RoHS, CCC, TUV

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看[www.barco.com.cn](http://www.barco.com.cn)以了解最新规格。