

ACS-2048

Alternative content switcher



Product specificaties

ACS-2048

General specifications

Ingangen	1x SDSDI per SMPTE 259M-C (NTSC/PAL resolution) and HDSDI Input and per SMPTE 292M (HDTV) 2 x DVI-I Inputs per DDWG 1.0 ■ HDCP support 1 x Analog Input on HD-15 VGA connector ■ Supports both YUV and RGBHV ■ 10-bits/color sampling (1:1 sampling up to 1600x1200@60 Hz) 1x Analog Input on BNC Connectors (5) ■ Supports both YUV and RGBHV ■ 10-bits/color sampling (1:1 sampling up to 1600x1200@60 Hz) 1x Composite NTSC/PAL Video (CVBS) on a BNC connector 1x Encoded NTSC/PAL Y/C Video on 4-pin mini-DIN connector 1x Optional Input (factory-installed mezzanine)
Uitgangen	DVI Dual channel ("Twin-Link DVI") output on 2 DVI-I connectors ■ 12-bit 4:4:4 RGB output ■ User selectable for 8-bit output ■ HDCP Encryption ■ Non-encrypted DVI data until HDCP is supported in the Projector Frame Rates: 50 Hz, 59.94 Hz
Gebruikersbediening	Front Panel Display ■ 128x32 VFD Display ■ Menu navigation via rotary encoder knob, Select/Escape buttons ■ Input Source selection via 9 back-lit buttons ■ Sync Present indication on Front Panel via switch backlight Remote Control ■ Fully controllable over IP
Mechanisch	Width: 19" Rack Height: 2RU Input connectors are located on front panel Output connectors are located on rear panel RJ45 connector is located on rear panel Handles (also provide mechanical protection of the inputs)
Vermogen	100-240 VAC – 50/60 Hz, Autoselecting 1.0A max

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

