

iQ G400



Spécifications techniques

IQ G400

Spécifications générales

Luminosité	4,200 ANSI lumen
Uniformité de la luminosité	Brightness uniformity: >95 % for the total screen
Panneaux LCD	3 active matrix 1.3" diagonal XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1024 x 768 pixels (aspect ratio 4:3). LCD panels are selected for a minimum of pixel defects.
Résolution	1024 x 768 (native)
Lampe	2x 250 Watt UHP lamp, in lamp housing, pre-aligned for max. light output. Typical lifetime: 1000 h/lamp. 1000 hours in Dual Lamp Mode or max. 2000 hours/set in Single Lamp Mode.
Lentilles	Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (long throw). Variable focus lenses with a throw distance of 1.3-1.8,1.9-2.6,3.0-6.0 times the screen width
Taille d'écran	From 1-6 m/3-20 ft.
Taux de contraste	>400 : 1 (full white/full black)
Fréquences de balayage	Horizontal 15 kHz -110 kHz Vertical 25 Hz -150 Hz
Caractéristiques	• Advanced picture-in-picture • Seamless switching with effects • Standard cable basket • Standard light shutter • Advanced digital zoom
Compatibilité	The iQ G400 is compatible with: • All current video sources (PAL,SECAM, NTSC) in Composite, S-VHS, Component or RGB formats • All currently proposed HDTV, extended and improved television standards (1080i, 720p) • All computer graphics formats from VGA, SVGA, XGA, SXGA to UXGA • Most Macintosh computers • Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz • Most computer sources with a pixel clock up to 160 MHz • DVI sources up to SXGA
Entrées	1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video , RGBHV, RGBS, RGsB. 1x Composite Video (BNC) (up to 7 Composite Video's when using all connectors on top input board) 1x S-Video (4-pin mini-DIN) (up to 3 S-Video's when combining BNC's) 1x VGA (D15 connector) 1x DVI (Digital Visual Interface)
Dimensions (l x l x H)	Projector body with cable basket: 415 mm (Max W) x 195 mm (Max H) x 565 mm (Max D) Projector body without cable basket: 415 mm (Max W) x 195 mm (Max H) x 487 mm (Max D)
Communication	1x D9 connectors for RS232 In/Out 1x spherical IR receiver
Niveau sonore	
Alimentation CA	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
Consommation électrique	Max 620 Watt
Dissipation d'énergie	Max 2117 BTU/h
Poids	Net weight: Body only 12.9 kg / 28.5 lbs. Shipping weight: • without lens max.17.5 kg / 38.5 lbs. • with lens: max.20 kg / 44 lbs.
Décalage de la lentille	QVD Lenses Motorized V shift: -30% +120% For specific details per lens type: see lens product pages
Commutation propre	Standard
Connexion réseau	Refer to iQ Pro G400

Crée le : 09 Jul 2024

© 2024 Barco nv. Tous droits réservés. La reproduction partielle ou intégrale sans autorisation écrite préalable est interdite. Les noms de marques ou de produits sont des marques commerciales, des marques déposées ou des appellations commerciales appartenant à leurs détenteurs respectifs. Pour des raisons d'innovation continue, les informations et les caractéristiques techniques sont susceptibles d'être modifiées sans préavis. Veuillez consulter www.barco.com pour les dernières spécifications.