

Barco Kroma MKII



Featuring our 2nd generation LED illumination system, Barco Kroma MKII produces a stunning, wide and extremely consistent color gamut and a rich, vibrant color rendition. With an unmatched 100,000 hour life expectancy, 13 lens options and close to unlimited installation flexibility, Barco Kroma MKII delivers the ultimate in image quality for smaller dedicated home cinema rooms.

技術仕様

BARCO KROMA MKII

一般仕様	
プロジェクタータイプ	2nd Generation Solid State LED DLP® projector.
光出力	up to 900 lumens
コントラスト比	Up to 8,000 : 1 (Infinite contrast and total black with Dynamic Black enabled)
レンズ群	0.61, 0.75-1.13, 1.12-1.58, 1.58-2.33, 2.37-3.79, 3.8-6.5 : 1
光学レンズシフト	adjustable: vertical and horizontal, depending on lenses
ランプ	LED
ランプ寿命 (標準)	LED Up to 100.000 hours
シールドエンジン	standard
互換性	"HDTV (1080p, 1080i, 720p), EDTV (576p, 480p), SDTV (576i, 480i), NTSC, PAL, SECAM, progressive scan"
3D	"active eyewear (optional), 2x optix cinemascope(stacked): INFITEC EX® 3D and Active Stereo IR, RF models, DLPLink™ "
入力	"2 x DVI-I, 2 x HDMI 1.3a, 2 x VGA 1 x Component, 1 x S-video"
制御	"1 x RJ-45 TCP/IP, 1 x 9-pin D-SUB RS232, 2 x 12V programmable trigger (3.5mm mini jack), 1 x Wired Remote 3.5mm mini jack, 2 x USB AMX Device Discovery, Crestron Certified Partner"
電源	6.5A, 200-240V, 50-60Hz
消費電力	"Certified rating: 8.4A, ~100-240V, 50-60Hz Typical consumption: Max 325W@100V, ~2.7A, 50Hz; ~1.2A, 240V, 50Hz"
動作温度	10 -40 °C
動作湿度/結露なし	20 -80% RH
BTU消失	less than 1,100
設置	table top, ceiling mount, straight down or up.
寸法 幅×長さ×高さ	510 x 376 x 223 mm excluding lens
重量	12.7 kg, shipping weight 20 kg
梱包サイズ	780 x 520 x 370 mm (WxHxD)
ハウジング・カラー	black and white
証明書	CCC, cCSAus, FCC Class A, cUL, UL and CE
保証	"limited 3 years warranty. Up to five years extended warranty available. Conditions apply."

生成日:09 Jul 2024

© 2024 Barco nv.(C) Barco. All rights reserved. (無断転載を禁ず。) 書面による許可なく全部または一部を複製することは禁止されています。すべてのブランド名および製品名は、それぞれの所有者の商標、登録商標、または商号です。継続的な技術革新により、情報および技術仕様は予告なく変更される場合があります。最新の仕様についてはwww.barco.comをご確認ください。

