

DP2K-32B

Bright DLP Barco Alchemy Cinema projector (33,000 lumens)



- Bright images, low operating cost
- Integrated, DCI-compliant projector
- Combines media server functionalities with Series 3 cinema processing electronics

Product specificaties**DP2K-32B**

General specifications	
Digital MicroMirror Device™	3 x 1.2" DC2K dark metal devices
Native resolutie	2,048 x 1,080 pixels
Behuizing	Hermetically sealed DMDs and optical assembly
Lamp	3kW -7kW (Xenon lamp)
Lichtuitvoer	33,000 lumens (6.5kW lamp factory installed) (more than 34,000 lumens using 7kW lamp)
Schermafmaat	Up to 32m / 105 ft wide
Contrastverhouding	2,000:1
I/O-controle	3x Ethernet 8x GPIO (DB 25) 3D interface USB RS-232 interface (DB9)
Integrated Cinema Media Processor	DCI 4K 2D up to 60fps* DCI 4K 3D (24 or 30 fps per eye)* DCI High Frame Rates 2K 3D up to 120fps (60fps per eye) JPEG 2000 bit-rates up to 625Mbps Dual-channel color-correction MPEG-2 (4:2:0 and 4:2:2 up to 60fps) 2x Displayport 2x 3G-SDI inputs 1x HDMI 1.4a (up to 4K 2D 24fps, support for BluRay 3D) 16x AES/EBU audio channels (2x RJ45) 8x GPI, 8x GPO (4x RJ45) 2x Gbe for content connectivity & ingest 2x front-accessible USB 3.0 for fast ingest 2x front-accessible USB 2.0 Video watermarking: Civolution NexGuard Audio watermarking: Civolution Closed captioning devices: Support for SMPTE 430-10 * 4K 24fps is standard. For 4K 60 fps / 4K 3D on ICMP upgrade modules a license is required. Newly-built 4K Barco Alchemy projectors have the license standard included.
Geïntegreerde opslag	1.9TB effective storage (RAID-5) / 3x 1TB Hot-swappable 2.5" hard-drives 3.9TB effective storage (RAID-5) / 3x 2TB Hot-swappable 2.5" hard-drives
Barco Web Commander	Projector Dashboard Projector Control Board Show Player/Editor/Scheduler Automation, 3D, Ingest Dynamic DCP playlists & intermission TMS integration Smart Projector Status Via HTML5 web-browsers including iOS & Android tablets Dual projector 3D: passive and active Auro 11.1 decoding

Product specificaties**DP2K-32B**

Barco Communicator	Projector installation & configuration Projector update & maintenance
Projectordiagnose	via Integrated Media Server via Communicator control software via SNMP agent
Voedingsvereisten	3x 400V + N or 3x 220V 30,000 BTU/hr (with 6.5kW lamp)
Afmetingen	604(H) x 754(W) x 1129(D) mm 23.78(H) x 29.69(W) x 44.45(D) inch NB.: min. 5 cm of air inlet spacing required at the bottom of projector
Gewicht	140 kg (309 lbs)
Omgevingstemperatuur	35°C / 95°F Max.
Luchtuitstroom	350 – 390 cfm (10 – 11 m ³ /min)
Opties	3D add-ons Touch screen monitor, inc. Barco Commander & Communicator Pedestal CineCare Web Auro 11.1 license Barco Escape license Live 3D*** *** Software roadmap
Veiligheidsvereisten	Class 1 risk group 3

Laatst bijgewerkt: 17 May 2023

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.