

FLD 3.8 - 6.5 : 1 (EN16)



Focus range: 4.0 - 40.0 m

Throw ratio

- SX+ 4.10-7.10:1
- 1080 / WUXGA 3.80-6.50:1

Product specifications**FLD 3.8 - 6.5 : 1 (EN16)****General specifications**

Working F/#	F 2.1-2.66 Motorized Iris F# 2.1-6.5
Zoom ratio	1.74 Motorized zoom and focus
Focal length	78.3-136.2 mm
Focus Range	Standard: 4m – 40m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	2.5 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">■ 1080p /Wuxga 3.8-6.5:1■ SXGA+ 4.1-7.1:1■ 720p 4.5-7.8:1■ XGA 5.6-9.7:1
	Image size tolerance +/-5%

Last updated: 29 May 2024

© 2024 Barco nv. Wszelkie prawa zastrzeżone. Powielanie w całości lub w części bez pisemnej zgody jest zabronione. Wszystkie nazwy marek i produktów są znakami towarowymi, zastrzeżonymi znakami towarowymi lub nazwami handlowymi odpowiednich właścicieli. Ze względu na ciągłe innowacje, informacje i specyfikacje techniczne mogą ulec zmianie bez wcześniejszego powiadomienia. Sprawdź www.barco.com, aby uzyskać najnowsze specyfikacje.

www.barco.com

BARCO