

# SP4K-12

12,000 lumens smart cinema projector



**12K**  
LUMENS

**4K**  
4096X2160

- **Brilliant image**
- **Ready for tomorrow, today**
- **Barco EcoPure™**
- **Fit and forget**

SP4K-12 is part of the Series 4 portfolio, designed in close collaboration with industry partners. Market trends in content creation, exhibition and technology were taken into account. The result? A next-generation laser projection family for all cinema screens. The SP4K models come in many different configurations offering you the freedom of choice. A wide range of brightness options, compatibility with Barco lenses and selected 3rd party lenses, as well as a touch display and live streaming option. Play with the available options to match your specific needs.

### **Brilliant image**

The SP4K models of the Series 4 family brings native 4K resolution, higher contrast and enhanced uniformity into the movie theater. The Barco Active Image Management™ includes patented technology to guarantee sharp, consistent image quality over time.

### **Ready for tomorrow, today**

With the SP4K models and their RGB laser lightsource, the Barco Colorgenic™ technology opens up more than 98.5% of Rec. 2020. Moreover, all SP4K models are fully enabled for future innovations like 4K 120fps and compatibility with the latest immersive audio standard.

### **Barco EcoPure™**

This silent running projector (50dB(A)) is fully ready for boothless operation. In addition, the SP4K-12 smartly manages its power consumption reaching projector efficiency levels up to 8 lumens per Watt. In eco-mode it consumes even less than 3 Watt. What's more, remote wake up on LAN is possible for scheduled maintenance or ingest.

### **Fit and forget**

The modular design of the Series 4 projectors allows for cost-effective maintenance. There are only six Barco laser plate™ spare parts to service all light source configurations. Anyone can replace the filters thanks to the toolless cover and filter handling. The SP4K-12 seamlessly integrates into your current setup.

**Product specifications****SP4K-12**

General specifications	
Native brightness	12,000 lumens (typical)
Native contrast ratio	2300:1 (typical) up to 3000:1 with HC lens
Digital MicroMirror Device™	3x 0.98" DC4K
Resolution	native 4K: 4096 x 2160
Color gamut	DCI P3 compliant (98.5% of Rec.2020; when measured in xy-color coordinates)
Light source	Laser
Prime lenses	With C-lensholder: 0.8 -1.16; 1.09 -1.40; 1.2 -1.8; 1.4 -2.05; 1.6 -2.5 ; 1.95 -3.2; 2.4 -3.9 With B-lensholder: 1.01; 1.27; 1.6 - 2.4; 1.9 - 2.6; 2.0 - 2.95; 2.3 - 3.65; 2.8 - 4.7; 3.55 - 6.95 High-brightness and High-contrast B-lenses compatible
Long-term brightness stability	40,000 hrs @ average usage conditions
Housing	integrated cooling design and patented sealed optical assembly
Dimensions (WxLxH)	Projector incl feet: 710 x 1070 x 547 mm/ 27,95 x 42,13 x 21,54 inches (710 x 1132x 547 mm/ 27,95 x 44.55x 21,54 inches with B-lensholder)
Weight	90kg / 198.5lbs
Power requirements	single phase or triple phase 200-240V 16A
Heat load (max. power)	4600 BTU/h
Exhaust airflow	300 CFM
Ambient temperature	40°C/104F Max.
Ambient humidity	85% RH max
Media server	Barco Alchemy ICMP-X and other media server brands** supported.
Power consumption	1.4kW (3W in Eco mode)
Noise Level	50dB(A) @1m and 25°C ambient temperature
3D systems	Active glasses systems and polarization systems on silver screens are supported. Color separation systems are not supported.
Safety requirements	Class 1 risk group 3
User interface	Touch Display and / or web-based
Lateral lens color on edge of image	With 2K lens: 2 pixels average* With 4K lens: 1.5 pixels average* (* depends on lens, zoom, ...)
Notes	**projector configuration with ICP-D; contact Barco service for the list of supported brands

Last updated: 13 May 2024

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.