

OverView OSV-711C

High brightness seamless 11.1 megapixels collaboration video wall



The OverView OSV-711C is a high-performing video wall that boosts high brightness levels. Featuring a large, curved, panoramic seamless canvas, a mix of data and video can be displayed simultaneously in high quality without the interruption of a seam or a bezel.

Furthermore, benefiting from advanced signal processing, the OSV offers a feature-rich solution with high image quality and excellent reliability. Compact in setup, this video wall suits a multitude of possible applications from crisis operations and war rooms, to brainstorm and planning rooms, and of more traditional control room applications in utilities, energy and process control.

Laser-phosphor projection for high brightness

Images are displayed on the OSV HB series using state-of-the-art laser-phosphor projection technology. This highly increases the system's brightness levels, allowing it to be used in environments with challenging lighting conditions. Additionally, this HB series has a higher resolution than its LL counterpart, offering 11.1 megapixels to display data. The OSV-711C consists of seven blended rear-projection cubes, forming one seamless image.

A real seamless canvas

No matter how thin, seams and bezels are always a nuisance. Especially when displaying numbers or other critical content, any interruption is too much. OSV's Seamless canvas makes sure a wealth of different sources can be positioned anywhere on the screen, in the most efficient way.

Saving real estate space

Compared with conventional rear-projection systems, the OSV video walls have a limited depth of less than 1.2 meters/47 inches. In this way, the available real estate

space is used to its maximum.

High brightness

The OSV HB series is equipped with laser-phosphor projection technology, strongly boosting its brightness levels. This allows the system to be used in environments with challenging lighting conditions.

Free from image retention

The OSV uses DLP technology, which is not sensitive to image retention. This means you can show static images without risking burn-in effects.

Enhanced immersive user participation

The use of a curved screen creates an immersive effect that makes everyone in the room feel more involved, which improves the collaboration.

More pixels

Compared with the OSV LL series, the OSV HB series has a 30% higher resolution. This means that even more information can be displayed on the seamless canvas.

Real-life collaboration

The large screen area, gives all participants in a telepresence meeting a front row seat. Using 3, 5 or 7 rear-projection modules, the horizontal size of the OSV system varies from 3.5 to 6.5 meters (120 to 240 inches).

Product specificaties**OVERVIEW OSV-711C**

General specifications	
Resolutie	11.1 Mega Pixels
Pixelgrootte	0.88 mm 0.035"
Systeemcontrast	50:1 with 100 lux ambient light on-screen
Kleur	95% REC709
Weergavetechnologie	Rear projection DLP
Wit punt	2,300K 6,500K 9,300K arbitrary
Helderheidsuniformiteit	85% ANSI 9
Scherf	Barco Semi-Rigid Seamless Rear Projection Screen
Ruimte tussen schermen	None. No seams or bezels
Scherfmaat	6233 (length) x 1400 (height) mm 245.4 (length) x 55 (height) inch
Radius	5384 mm / 212 inch (screen)
H / V Half Gain-hoek	60° both horizontal and vertical
Scherfreflectiviteit	2%
Afmetingen (fysiek)	7720 (length) x 2370 (height) mm 304 (length) x 93.3 (height) inch
Beginhoogte beeld	750 mm / 29.5 inch above floor
Diepte	Center: 1172 mm / 46 inch
Gewicht	1205 kg / 2657 lbs
Lichtbron	Laser phosphor illumination
Levensduur lichtbron	20,000 h (normal mode)
Aanbevolen onderhoudsinterval	3 / year . No burn-in, no image retention
Gebruiksomstandigheden	0°C-35°C / 32°F-95°F 80% humidity (non condensing)
Ingangsspanning (wisselstroom)	110 – 240 V, 50-60Hz
Vermogen	Typical : 2900 W ; Maximum : 3720 W
Warmteafvoer	Typical : 9905 BTU/h ; Maximum : 12705 BTU/h
Signaalingangen	Twin dual link DVI-D
Ingangsfrequentie	300 MHz
Garantie	2 years

Laatst bijgewerkt: 15 Mar 2023

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.