


# XT 110" LED Video Wall

Complete Full HD LED video wall package



- All-in-one package
- Pre-configured
- Easy to order
- Full HD resolution

This all-in-one package not only contains the necessary LED panels to build a Full High-Definition video display, but it also includes our in-house developed image processing Infinipix™, all data & power cables and wall mounting structure. In other words, everything you need to build your LED video wall in the fastest way possible.

### **An easier way to an impressive LED display**

This pre-configured package includes XT 1.2 LED panels, image processing, cables and mounting structure. With best-in-class image quality and 800 nits brightness, the XT series guarantees a superior viewing experience. What's more, the camera-based seam compensation technology guarantees a uniform seamless canvas viewing experience.

As a result of the Infinipix™ image processing system, the display's image quality is perfect in both dimmed and high-brightness modes with consistent Rec. 709 color accuracy. Video artifacts typically arise on fast-moving content, but with Infinipix™, no image tearing or video hiccups occur. Additionally, Barco's automatic calibration ensures the entire video wall is always perfectly uniform.

The included mounting structure enables the LED display to be mounted directly to the wall, which yields a shallow depth video display. The improved robustness and the Assisted Module Extraction allow the tiles to be removed easily, for maintenance or replacement needs, limiting the risk of pixel damage.

### **Expanding your LED experience**

In order to support the use of direct-view LED in critical environments and prevent downtime, optional redundancy of both power and data can be integrated in the XT1.2. In order to perform advanced screen management, Barco also has an extended screen management portfolio which can be combined with your LED display.

All XT series displays are backed by our standard three-year product warranty. For extra peace of mind, customers can choose an additional EssentialCare maintenance contract with batch-compatible modules up to seven years.

**Product specificaties****XT 110" LED VIDEO WALL**

LED tiles	
Weergavetechnologie	Direct view LED
Resolutie	Full HD (1920 x 1080 px)
Beeldschermgrootte	110" (diagonal)
Pixelpitch	1.2 mm
Helderheid	> 800 nit
Contrast	>9,000:1
Emissie blauw licht	Patented driver algorithm to reduce eye fatigue
Helderheidsuniformiteit	>98%
Interne verwerking	23 bit
Kleuren	16 bit (281 trillion)
Kleuruniformiteit	xy +/-0.005
Voldoet aan REC 709	yes
Vernieuwingsnelheid	3840 Hz
Kleurtemperatuur	3000 - 9300k (adjustable)
Hor. kijkhoek	155° +/-5° (@50% brightness)
Vert. kijkhoek	145° +/-5° (@50% brightness)
Video-ingangsresolutie	1920 x 1080 px @60Hz - 8/10/12 bit 1920 x 1080 px @120Hz - 8 bit
Video-ingangen	HDMI (HDCP enabled) - SDI
3D	Yes
HDR	HLG / HDR10
Content windowing	1
Controle	Network - cloud based software management
Runtime duty cycle	24/7
Led-levensduur	100,000h (video - 50% brightness)
Redundantie	Data and power (optional)
Netspanning	100 - 240 VAC, 50 - 60 Hz
Energieverbruik	1042 W (typical) 2246 W (max)
Warmtedissipatie	3450 BTU/hr (typical) 8043 BTU/hr (max)
Gewicht	120 kg / 264.6 lbs
Milieuspecificaties	Indoor
Opslagtemperatuur	-20°C to 50°C / -4°F to 122°F
Vochtigheid bij opslag	10 -80%
Bedrijfstemperatuur	-10°C to +40°C / 14°F to 104°F
Operationele vochtigheid	10 - 80%

**Laatst bijgewerkt: 22 Jun 2023**

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg [www.barco.com](http://www.barco.com) voor de meest recente specificaties.