

F50 WUXGA

Compact 120 Hz, single-chip DLP projector with WUXGA resolution



- **Razor-sharp images with vivid colors**
- **Active 3D stereo and high frame rates**
- **Compact and rugged design**

Designed for 24/7 operation, the F50's total cost of ownership is reduced to a minimum thanks to its reliable DLP® technology, filter-free design, and low maintenance needs. The compact F50 projector is suited for a wide variety of demanding applications in virtual reality, simulation and training, visitor attractions, collaboration suites and scientific visualization.

Unmatched image quality

With its cutting-edge optics that deliver razor-sharp images, the F50 displays flawless images with vivid colors, and rich in contrast. Producing low noise levels, it also features RealColor™ color management, Smear Reduction Processing™ and high frame rates. The F50 boasts four different digital input sources and a wide range of expansion modules and high-quality projection lenses.

Key benefits

- Small, compact and ruggedized
- Ultimate reliability and low TCO
- Low operational noise level
- Active 3D stereo
- Smear Reduction Processing™/ 120Hz Refresh Rates / High Frame Rates

Product specificaties**F50 WUXGA****General specifications**

Type projector	Single chip DLP digital projector
Technologie	LVDS DMD™ with DarkChip3™
Resolutie	1920 x 1200
Helderheid	5,500 ANSI lumens (High Brightness) 2,700 ANSI lumens (VizSim Bright) 2,000 ANSI lumens (VizSim)
Contrastverhouding	up to 5,300:1
Helderheidsuniformiteit	>80%
Beeldverhouding	16:10
Type lens	All pure glass lenses
Lenzen	Ultra Wide Fixed EN53 (0.74:1 @1.65m) Wide Fixed EN52 (0.92:1) Super Wide Zoom EN55 (0.80 -1.08:1) Wide Zoom EN56 (1.06 -1.62:1) Zoom EN51 (1.60-2.21:1) Ultra short throw EN57 (0.28:1)
Optische lensverschuiving	Vertical up to 110%, depending on lens Horizontal up to 52%, depending on lens Motorized lens shift
Kleurcorrectie	RealColor™
Lampen	1 x 350W UHP (dimmable)
Levensduur lamp	Up to 2,000 hours (Full power) / up to 2,500 hours (Eco mode)
Lampbehuizing, snelle vervanging	Yes
Lampgarantie	500 hours or 90 days
Verzegelde DLP™-kern	Yes
Oriëntatie	Table -ceiling (360 degrees through lamp axis)
3D	Up to 2,560 x 1,600 @ 120Hz
Ingangen	2x DisplayPort 1.2 (HBR2), 1 x DVI-Dual Link, 1 x HDMI 1.4a, 1 x VGA, 2x 3G-SDI, 1x HDBaseT
Invoerresoluties	2,560 x 1,600 -640 x 480 pixel resolution, RGBHV, RGBS, RGsB, custom formats available, HDTV (1080p, 1080i, 720p), NTSC, PAL, SECAM
Max. pixelklok	Up to 600 Mhz (2,560 x 1,600@120 Hz max) DP 1.2 Up to 330 Mhz Dual link DVI
Softwaretools	SimCAD, Projector Toolset
Controle	IR, RS232, Ethernet, USBA, 2x BNC sync, 1x MiniDIN
Netwerkverbinding	10/100/1000 base-T, RJ-45 connection, RS-232
Voedingsvereisten	100-240V 50-60Hz
Energieverbruik	less than 530W
Operationele omgevingstemperatuur	10 -40 °C /50 -104 °F, 0-3,000m (Storage temperature: -20 -60 °C/-4 -140 °F)
Vochtigheid in bedrijf	20 -80% RH (Storage Conditions: 10 -90% RH)
Dissipatie BTU	max 1,807 BTU/h
Afmetingen (B x L x H)	342 x 306 x 143 mm / 13.46 x 12.05 x 5.63 in
Gewicht	7.5 kg / 16.5 lbs
Standaardaccessoires	Power cord, wireless remote control
Certificeringen	Compliant with FCC, part 15 Class A and CCC, cNus, cUL, UL and CE
Garantie	Limited 3 years parts and labour

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.