

# BARCOVision 8200



**Product specifications****BARCOVISION 8200****General specifications**

Contrast	5x4 Checkerboard: 120:1 Full Field Contrast: 300:1
Depth	1162 mm / 46 inch
Height	366 mm / 14 inch
Inputs	Communication: 1 D9-female Stereo Audio: 2 x Cinch (RCA) RGB trilevel sync, sync on green or sync separate: 5 x BNC (Optional) RGB analog standard sync, sync on green or sync separate or composite sync: 5 x BNC (Optional) Component Video: 4 x BNC (Optional) Video/S-Video: 1 x BNC/4-pin DIN (Optional) RS232 loop-through: 1 x D9-female
Light output	2500 ANSI Lumen
Outputs	RS232 loop-through: 1 x D9-male
Resolution	Maximum Resolution through windowing: 800 x 600
Screen size	Minimum Screen Width 1m Maximum Screen Width 5m
Weight	Net weight: 70 kg / 154 lbs Shipping weight: 110 kg / 243 lbs
Width	630 mm / 25 inch

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.