

# BARCOVision 508



**Product specifications****BARCOVISION 508****General specifications**

Compatibility	Video (PAL, SECAM, NTSC 3.58, 4.43) 4-pin S-Video RGB or Component Video
Contrast	>1000:1 (full white/full black)
Light output	1100 Lumen at 10 % peak white 160 ANSI lumen
Screen size	Min.: 4.6' x 3.5' (4:3 aspect ratio) -4.6' x 2.6' (16:9 aspect ratio) Max.: 23' x 17.3' (4:3 aspect ratio) -23' x 12.9' (16:9 aspect ratio)

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.