

CVWU-31B

3,000 lumens, WUXGA, single-chip DLP projector



- Razor-sharp images with vibrant colors
- Large lens shift range for flexible installation
- Compact design
- 24/7 reliability

*Only available at selected distributors

Thanks to its compact white design, the CVWU-31B seamlessly blends in with your meeting room, boardroom or small auditorium.

A compact projector

Did you know that similar projectors with the same features weigh about 17% more and are about 45% bigger than the CVWU-31B projector? It combines ultimate image quality in a very small form factor.

Impressive images, crisp colors

Offering 3,000 lumens light output and native WUXGA resolution, it delivers crystal-clear and high-contrast images with excellent brightness uniformity at a low noise level. When configured with a high-brightness color wheel, the CVWU-31B projector provides brilliant pictures with vivid colors.

Built to last

The CVWU-31B features a filter-free design and reliable DLP® technology for unmatched picture accuracy and low total cost of ownership. Designed for unlimited use, it also comes with a three-year warranty, for true peace of mind.

Product specificaties**CVWU-31B****General specifications**

Technologie	Optical lens shift design
Resolutie	1,920 x 1,200 (WUXGA)
Helderheid	3,000 ANSI lumens
Type projector	Single-chip DLP projector
Contrastverhouding	2,500 : 1
Helderheidsuniformiteit	>80%
Beeldverhouding	16:10
Type lens	All glass lenses
Lenzen	Standard Zoom lens (1.64-2.06:1)
Optische lensverschuiving	Vertical
Kleurcorrectie	RealColor™
Lampen	220W UHP lamp
Levensduur lamp	Up to 2,250 hours (full power) / 3,000 hours (eco mode)
Lampbehuizing, snelle vervanging	Yes
Lampgarantie	500 hours or 90 days
Verzegelde DLP™-kern	Yes
Oriëntatie	Table – ceiling (360 degrees through portrait mode)
3D	No
Ingangen	1 x HDMI (1.3), 1 x DVI-D, 1 x VGA, 1x RCA composite video, 1 x 4-pin mini DIN Y/C, 1 x RCS x3 YUV
Invoerresoluties	1,920 x 1,200 -640 x 480 pixel resolution (model dependent) / RGBHV, RGBS, RGsB
Softwaretools	Projector Toolset
Controle	IR, RS232, Ethernet
Netwerkverbinding	1 x RJ-45 TCP/IP, 1 x 9-pin D-SUB RS232, 1 x USB
Voedingsvereisten	3.0-1.3A, ~100-240V, 50-60Hz
Energieverbruik	Max 290W
Geluidsniveau	30 dB
Operationele omgevingstemperatuur	10 -40 °C (storage temperature: -20 -60 °C)
Vochtigheid in bedrijf	20 -80% RH
Dissipatie BTU	Less than 1,061/hour
Afmetingen (B x L x H)	278 x 234 x 94 mm / 10.94 x 9.21 x 3.70 inches
Gewicht	2.9 kg (6.39 lbs)
Standaardaccessoires	Power cord, wireless remote control
Certificeringen	CE, FCC Class A and cCSAus
Garantie	Limited 3 years parts and labor. Extendable up to 5.

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.