

FLD lens (1.24 - 1.6 : 1) EN13 (optimized for WUXGA)



- WUXGA = 1.24 - 1.60 : 1 (F70 W, F90 W)
- 1080p = 1.24 - 1.60 : 1
- SXGA = 1.34 - 1.73 : 1
- 720p = 1.47 - 1.89 : 1
- XGA = 1.84 - 2.37 : 1

Product specifications**FLD LENS (1.24 - 1.6 : 1) EN13 (OPTIMIZED FOR WUXGA RESOLUTION)****General specifications**

Working F/#	F 2.1-2.22 Motorized Iris F# 2.1-6.5
Zoom ratio	1.3 Motorized zoom and focus
Focal length	25.59-33.24 mm
Focus Range	Standard: 1.0m – 15m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	2.6 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">■ 1080p/WUXGA 1.24-1.6:1■ SXGA+ 1.34-1.74:1■ 720p 1.46-1.9:1■ XGA 1.83-2.37:1
	Image size tolerance +/-5%

Last updated: 13 Jun 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.