

Fiberlink

Adds fiber-optic technology to the solution for guaranteed quality of the final picture with a reach up to 300 meters.



Product specifications**FIBERLINK****General specifications**

Reach	300 meter cascable
Signal	<ul style="list-style-type: none">▪ 1,5 Gig/sec▪ no compression▪ full quality stream to LED display▪ Proprietary transmission▪ error detection and correction protocol
Outdoor Compliance	IP 65 fiberoptic connectors

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.