

D-Cine Premiere DP100

2k Digital Cinema projector for large screens up to 20m (65.6ft)



기술 사양

D-CINE PREMIERE DP100

일반 사양

광 출력	22,000 cinema lumens
Digital MicroMirror Device™	3 x 1.2" dark metal type Advanced DLP Cinema™ signal processing: CineCanvas™ image management; CinePalette™ color management, CineBlack™ contrast management and CineLink™ security management
기본 해상도	2048 x 1080
하우징	Hermetically sealed DMD™ and optical assembly
스크린 너비	Screen width (screen gain 1:8) @ 14ftL: 25m -82ft adjustable light output CLO software
장착	Standing on pedestal, including caster & wheels Up to 15 degrees tilt on pedestal
램프	1.5k to 7k Xenon arc lamp sizes Compatible with standard and high performance lamp types
명암비율	2000:1
디지털 비디오 입력	2 x SMPTE 292M inputs 2 x DVI input both selectable as single or as dual link
최고급 렌즈	M25 1.25 -1.45:1 / M25 1.45 -1.8:1 / M25 1.8 -2.2:1 / M25 2.2 -3.0:1 zoom and M25 3.0 -4.3:1
프로젝터 진단	Via touch screen Via D-Cine Communicator control software (theater edition delivered standard on every product) Via SNMP agent
전원 요구 사항	3 x 400V + N or 3 x 220V version available max. 29,250 BTU/hr (with 6.5kW lamp)
크기	projector head: 640(H) x 730(W) x 1186(D) mm / 24.2(H) x 28.7(W) x 46.7(D) inch projector head + pedestal: 1466(H) x 730(W) x 1252(D) mm / 57.7(H) x 28.7(W) x 49.3(D) inch
무게	projector head + pedestal: approx. 205kg (452lb)
옵션	· CLO -Constant Light Output control · Anamorphic lens fitting for 1.25:1 scope lens · Acsar 2 Alternative Content Input Processor · ImagePRO HD · SNMP agent (v3)
주문 정보	EU: R9010111 US: R9010118

작성일: 09 Jul 2024

© 2024 Barco nv. All rights reserved. 서면 허가 없이 전체 또는 부분을 복제하는 것은 금지됩니다. 모든 브랜드명 및 제품명은 상표, 등록 상표 또는 해당 소유자의 상표입니다. 지속적인 혁신으로 인해 정보 및 기술 사양은 사전 고지 없이 변경될 수 있습니다. 최신 사양은 www.barco.com을(를) 확인하세요.