

SLM R6 Performer

A Compact and Smokeproof Projector for Rental & Staging Applications



- Enhanced low-light video performance is the result of its newly designed pixel map processor.
- Integrated linked Constant Light Output (CLO), which can be linked with other R6 projectors for use in multi-screen applications.
- True seamless switching includes transition effects such as cross-fade, wipe, etc. and Picture-In-Picture capability.
- The unique "click-and-play™" lenses make it possible to exchange lenses in seconds. Carrying handle with integrated rigging system. Direct stacking and interlocking design enable an easy and stable setup.
- Sealed optics significantly reduce optical system maintenance, which allows the R6 to be used at events where smoke generators are involved. Modular structure provides greater accessibility to serviceable parts.
- The optical system's compact and lightweight lens range is designed for the continuing evolution of the DLP technology.

Specifiche tecniche

SLM R6 PERFORMER

Specifiche generali	
Emissione luminosa	5.000 ANSI lumens
Digital MicroMirror Device™	3 high resolution SXGA DMDI's
Risoluzione	1280 x 1024 (native) 1600 x 1200 (max)
Uniformità della luminosità	> 90% for the total screen area
Contrasto	800:1 (full white/full black)
Lampada	Lifetime (max): 1500 Hrs Lifetime (typ): 1000 Hrs Lamp power: 1,2 kW
Livello di rumore (a 20° C)	< 43
Livello di rumore (a 40° C)	< 50
Tensione di alimentazione	110/230 V
Consumo energetico	1.600 W
Temperatura ambiente	40°C (104F) max
Dimensioni	875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9"
Peso (compresi elementi di assemblaggio)	56 kg / 124 lbs
Ottiche	BARCO's "click-and-play" TLD lenses provide the highest quality picture. Available both in fixed and zoom versions.
Spostamento obiettivo	Motorized V shift: up to 100% Motorized H shift: up to 65%
Elemento centrale DLP™ sigillato	Yes
Commutazione continua	Standard
ScenergiX	Standard
Ingressi fissi	<ul style="list-style-type: none">· 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals· 2 Multistandard DVI· SDI input (Serial Digital Input)
Ingressi opzionali	One free digital input slot for optional input modules: <ul style="list-style-type: none">· SDI· HD -SDI
Comando da remoto	<ul style="list-style-type: none">· RS232 or RS422 loop-through input (D9-connector) for PC based projector control· Communication input (D9-connector) for peripherals· 3 pin male XLR connector for wired remote (standard remote)· 3 pin female XLR connector for bi-directional communication (rugged remote)

Generato il: 15 Mar 2023

Le informazioni e i dati forniti riguardano l'apparecchiatura descritta. Tuttavia ogni singolo articolo è soggetto a modifiche senza preavviso.
 L'ultima versione di questo opuscolo è disponibile all'indirizzo www.barco.com.