

MiPIX-20

Small creative LED block to enable you to build LED displays of any shape and form.



Product specificaties

MIPIX-20

General specifications	
Pixelpitch	20 mm
Helderheid	1.300 NIT
Led-configuratie	4 SMD LEDs (2x2 configuration)
Hor. kijkhoek	145° (min 50% brightness)
Vert. kijkhoek	145° (min 50% brightness)
Contrastverhouding	950:1 (500 lux)
Levensduur	45.000 hours (50% brightness full white)
Energieverbruik	1.2 W / block (max) 206W / system (1 CU + 128 blocks)
Afmetingen	40.3 x 40.3 x 22 mm (WxHxD)
Gewicht	34g
Verwerking	14 bit
Vernieuwingssnelheid	1045 Hz
Bedrijfstemperatuur	0 to 40°C (32 to 104°F)
Opslagtemperatuur	-20 to 60°C (-4 to 140°F)
Vochtigheid in bedrijf	0 to 85%
Vochtigheid bij opslag	0 -90%
Broncompatibiliteit	S-Video, Composite, YUV, RGB, SDI, HDSDI, Data DVI up to SXGA
Structuur	Plugs into metal structure, can handle multiple inserts

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

