


DP2K-6E

Compact DLP Barco Alchemy Cinema projector for screens up to 7.5m (24ft) wide



- **Twice as quiet as the quietest digital cinema projector**
- **Simple UHP lamp swap for easy maintenance**
- **Fully integrated and DCI-compliant projector**

Taking digital cinema where it's never gone before

The DP2K-6E brings compact, fully integrated and DCI compliant digital cinema projection to small and independent cinemas worldwide. And how!

Why you'll love the DP2K-6E

- Cost-effective and fully integrated thanks to its on-board Barco Alchemy Series 3 module
- UHP lamps enable easy maintenance and compact design
- Twice as silent as the quietest projector currently on the market and super compact
- Trademark Barco quality, and modularity, now also for the smallest screens

Series 3 electronics combining media server functionality with cinema processing electronics Fewer boxes lead to higher reliability and ease-of-use Simple operation thanks to the intuitive 'Barco Web Commander' user interface

- Series 3 electronics combining media server functionality with cinema processing electronics
- Fewer boxes lead to higher reliability and ease-of-use
- Simple operation thanks to the intuitive 'Barco Web Commander' user interface

Product specificaties**DP2K-6E****General specifications**

Native resolutie	2,048 x 1,080 pixels
Behuizing	Hermetically sealed DMDs and optical assembly
Lichtuitvoer	DCI colors: 4,800 lumens / Non-DCI: 7,200 lumens
Lampen	Dual 465W, UHP lamps
Schermmformaat	Up to 7.5m/24.6 ft wide (screen gain 1.2 @ 14ftl)
Contrastverhouding	1,600:1
Digital MicroMirror Device™	3 x 0.69" DC2K dark metal devices
Primelenzen	Fully motorized 1.2 -1.7 1.34 -1.9 1.5 -2.15 1.7 -2.55 2.0 -3.9
I/O-controle	3x Ethernet (RJ 45) 8x GPIO (DB 25) 3D interface USB interface
Integrated Cinema Media Processor	DCI 4K 2D up to 60fps* DCI 4K 3D (24 or 30 fps per eye)* DCI High Frame Rates 2K 3D up to 120fps (60fps per eye) JPEG 2000 bit-rates up to 625Mbps Dual-channel color-correction MPEG-2 (4:2:0 and 4:2:2 up to 60fps) 2x Displayport 2x 3G-SDI inputs 1x HDMI 1.4a (up to 4K 2D 24fps, support for BluRay 3D) 16x AES/EBU audio channels (2x RJ45) 8x GPI, 8x GPO (4x RJ45) 2x Gbe for content connectivity & ingest 2x front-accessible USB 3.0 for fast ingest 2x front-accessible USB 2.0 Video watermarking: Civolution NexGuard Audio watermarking: Civolution Closed captioning devices: Support for SMPTE 430-10 * 4K 24fps is standard. For 4K 60 fps / 4K 3D on ICMP upgrade modules a license is required. Newly-built 4K Barco Alchemy projectors have the license standard included.
Geïntegreerde opslag	1.9TB effective storage (RAID-5) / 3x 1TB Hot-swappable 2.5" hard-drives 3.9TB effective storage (RAID-5) / 3x 2TB Hot-swappable 2.5" hard-drives
Barco Web Commander	Projector Dashboard Projector Control Board Show Player/Editor/Scheduler Automation, 3D, Ingest TMS integration Smart Projector Status Via HTML5 web-browsers including iOS & Android tablets
Barco Communicator	Projector installation & configuration Projector update & maintenance
Voedingsvereisten	200-240 VAC
Projectorafmetingen (H x B x D)	369 x 689 x 664 mm 14.5 x 27.1 x 26.1 inch
Projectorgewicht	53.8 kg / 119 lbs (including recessed handles for easy carrying)
Omgevingstemperatuur	35°C / 95°F Max.
Opties	3D add-ons Touch screen monitor, inc. Barco Commander & Communicator Pedestal CineCare Web Auro 11.1 license Barco Escape license Live 3D*** Ceiling mount kit*** (***) roadmap
Geluidsniveau	48 dB(A)
Luchtstroomvereisten	43 CFM

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

www.barco.com**BARCO**