


# E2 Jr

Cost-effective Event Master processor



- **Easy and reliable show setup and production**
- **Market-valued 4K performance**
- **Future-proof upgradability to the full E2 system**

Bringing the same performance and features as the E2, the E2 Jr model is ideally suited for applications that do not require the full capacity of the E2. Offering 16 inputs, 8 outputs, and 8 mixers (or 16 single layers), the E2 Jr features the same 4 RU form factor as its bigger E2 brother.

### Easy upgrading

Thanks to its modular design E2 grows with your shows so you can easily upgrade the E2 Jr to a fully loaded E2 system at any time. You can simply purchase and install additional cards into your system. This modularity also ensures great serviceability, as users can easily swap a specific input or output card in the case of damage, without needing to ship or replace the entire box.

### Designed for life on the road

Designed for the live event industry, the rugged E2 Jr features a steel chassis that's able to withstand the challenging conditions of life on the road. What's more, it offers screen control in a compact form factor of only four rack units, which makes it easy to ship and install. And thanks to its modular cards and dual redundant power supplies, the E2 Jr is extremely reliable and easy to service in the field.

## Product specificaties

## E2 JR

### General specifications

|                                   |   |
|-----------------------------------|---|
| Model                             | NGS-4U  |
| Live-effectencanvas               | Up to 10 Megapixels PVW/PGM 20 Megapixels PGM only 40 Megapixels @30p and PGM only  |
| Video-ingangen                    | 16 inputs via 4 input cards (Event Master series cards) <ul style="list-style-type: none"><li>Up to 4 x 4K inputs - each input card supports up to 4K@60p</li><li>4 x SD/HD/3G SDI</li><li>6 x HDMI 1.4a (297 Mpix/sec max)</li><li>6 x DisplayPort 1.1 (330 Mpix/sec max)</li></ul>                        |
| Video-uitgangen                   | 10 outputs via 3 output cards (Event Master series cards) <ul style="list-style-type: none"><li>Up to 2 x 4K outputs - each output card supports up to 4K@60 p</li><li>4 x SD/HD/3G SDI</li><li>4 x HDMI 1.4a (297 Mpix/sec max)</li><li>2 x HDMI 1.4a for Multiviewer (297 Mpix/sec max)</li></ul>         |
| Genlock                           | Analog reference input/loop on BNC connectors; bi-level and blackburst at SD and tri-level at HD<br>S3D Sync: 4x input Din connector, 2x output Din connector   |
| Programma-uitvoer                 | Up to 8 program outputs configurable as single screens or tiled/blended widescreens <ul style="list-style-type: none"><li>Configurable for up to 8X 2048X1200@60 max or up to 2 x 4096x2400@60 max</li><li>Independent edge blending/feathering control for all four sides</li></ul>                        |
| Aux-uitgangen met schaalverdeling | User definable from 4 x 2048x1200@60 to 1 x 4K@60<br>All outputs can be defined as Aux destinations for a total of 8 Aux outputs<br>Output color correction   |
| Mixers                            | <ul style="list-style-type: none"><li>Native resolution background mixer per output screen</li><li>Independent layer transitions or full Preview/Program transition</li><li>Flexible layer allocation – up to 8 mixable or 16 single scalable PIP/key layers assignable to Program output screens</li></ul> |
| Geheugenruimte voor foto's        | Up to 100 HD stills available in background, Aux or PIP   |
| Laageffecten                      | <ul style="list-style-type: none"><li>Borders (hard, soft, halo) and drop shadows</li><li>Color effects</li><li>Strobe, H&amp;V flip</li><li>Luma key</li><li>PIP moves via Keyframes</li></ul>   |
| Multiviewer                       | <ul style="list-style-type: none"><li>Flexible user-definable layouts</li><li>Monitor all Inputs and Outputs, including Preview and Aux</li><li>Two outputs</li><li>Dedicated hardware same E2 Event Master Processors</li></ul>  |
| Uitbreidbaarheid                  | Linking is available as an upgrade option   |
| HDCP                              | HDCP compliant  |
| Controle                          | <ul style="list-style-type: none"><li>Event Master screen management software for PC or MAC</li><li>Ethernet RJ-45, 1000/100/10 Mbps autosense</li></ul>  |
| Onderhoudsgemak                   | <ul style="list-style-type: none"><li>Field-serviceable I/O and processing cards (not hot-swappable)</li><li>Hot-swappable dual-redundant power supplies</li></ul>  |
| Geluidsniveau                     | Max 52.9 dB avg. Fans at 100%. Fan speed is software managed based on operating temperature. Reference ISO 7779   |
| Afmetingen                        | <ul style="list-style-type: none"><li>Height: 17.8 cm (7.0 in) - 4 RU rack mount</li><li>Width: 43.2 cm (17 in) without chassis handles, 48.3 cm (19 in) with chassis handles attached</li><li>Depth: 56.9 cm (22.4 in) from front panel to rear panel, 62.2 cm (24.5 in) overall</li></ul>                 |
| Gewicht                           | 27.8 kg / 61 lbs  |
| Vermogen                          | <ul style="list-style-type: none"><li>Input power: 100-240 VAC 50/60Hz 700W</li><li>Dual-redundant, hot-swappable power supplies</li></ul>  |
| Garantie                          | 3 years parts and labor   |
| Omgevingstemperatuur              | 0-40° C / 32-104 F  |
| Omgevingsvochtigheid              | 0-95% non-condensing  |

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer [www.barco.com](http://www.barco.com) voor de nieuwste specificaties.