

FLDX 0.8 - 1.21 : 1 (EN66)

Short focus



Focus range: 0.7 - 7.0 m

Throw ratio

- WUXGA 0.75 - 1.13 : 1
- WQXGA/4K 0.80 - 1.21 : 1
- F80: 1.06 - 1.60 : 1 (WQXGA/4K UHD) (F80 requires lens adapter R9801442)
- F400-HR: 0.71 - 1.06 (native 4K) (Requires the use of individual F400-lens adapters)

Product specifications**FLDX 0.8 - 1.21 : 1 (EN66) SHORT FOCUS**

General specifications	
Platforms	For F35, FL40, F70, F80* and F90 projector series *requires lens adapter R9801442. F80 specific throw ratio: 1.06 -1.60 : 1 (WQXGA/4K UHD)
Working F/#	F 2.4-3.29 Motorized Iris F# 2.4-6.5 with memory
Zoom ratio	1.51 Motorized zoom and focus with memory
Focal length	15.98-23.99 mm
Focus Range	0.7-7.0 m
Weight	3.3 kg
Shipping weight	4.0 kg
Throw Ratio	DMD chip WUXGA 0.75 -1.13 : 1 WQXGA 0.80 -1.21 : 1 Image size tolerance +/-2%

Last updated: 15 Mar 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.