

FLDX 0.8 - 1.21 : 1 (EN66)

Short focus



Focus range: 0.7 - 7.0 m Throw ratio

- WUXGA 0.75 - 1.13 : 1
- WQXGA/4K 0.80 - 1.21 : 1
- F80: 1.06 - 1.60 : 1 (WQXGA/4K UHD) (F80 requires lens adapter R9801442)
- F400-N4K: 0.71 - 1.06 (Requires the use of individual F400-lens adapters)

Product specifications**FLDX 0.8 - 1.21 : 1 (EN66) SHORT FOCUS****General specifications**

Platforms	For F35, FL40, F70, F80* and F90 projector series *requires lens adapter R9801442. F80 specific throw ratio: 1.06 -1.60 : 1 (WQXGA/4K UHD)
Working F/#	F 2.4-3.29 Motorized Iris F# 2.4-6.5 with memory
Zoom ratio	1.51 Motorized zoom and focus with memory
Focal length	15.98-23.99 mm
Focus Range	0.7-7.0 m
Weight	3.3 kg
Shipping weight	4.0 kg
Throw Ratio	DMD chip WUXGA 0.75 -1.13 : 1 WQXGA 0.80 -1.21 : 1 Image size tolerance +/-2%

Last updated: 05 Nov 2024

© 2024 Barco nv. Wszelkie prawa zastrzeżone. Powielanie w całości lub w części bez pisemnej zgody jest zabronione. Wszystkie nazwy marek i produktów są znakami towarowymi, zastrzeżonymi znakami towarowymi lub nazwami handlowymi odpowiednich właścicieli. Ze względu na ciągłe innowacje, informacje i specyfikacje techniczne mogą ulec zmianie bez wcześniejszego powiadomienia. Sprawdź www.barco.com, aby uzyskać najnowsze specyfikacje.

www.barco.com

BARCO