

LX-5

10 megapixel, 4,500 lumens LCoS projector



Product specifications

LX-5

General specifications

Light output	up to 4,500 lumens
Contrast ratio	>10,000:1
Resolution	4096x2400 (10 megapixel)
Display	LCoS
Lamp	800W xenon
Lamp lifetime	750h warranted, max 1500h
Weight	<ul style="list-style-type: none">50kg / 110lbs (net)65kg / 143lbs (shipping)
Dimensions	<ul style="list-style-type: none">Height: 390mm / 15.35"Width: 660mm / 25.98"Length: 830mm / 32.68"
Lens Shift	<ul style="list-style-type: none">Horizontal up to +/- 60%Vertical up to +/- 100%
Standard inputs	4x dual DVI-D (up to 12 bit)
Communication Port	<ul style="list-style-type: none">USB portRS232C (D-9 connector)1x 10/100 Mb/s Ethernet RJ45
Computer graphics formats	All computer graphic formays from VGA, SVGA, XGA, SXGA, UXGA, 1080p HD, QXGA, WUXGA, 1080p HD, 2K, QHD, 4K up to 10MP
Safety	<ul style="list-style-type: none">UL60950CE compliantRoHS and WEEE compliant
Max. power consumption	1500 Watt
Special Features	<ul style="list-style-type: none">Up to 4 PaP (picture-and-picture) data and image windowsAdjustable color temperatureLamp economy modeHigh dynamic range compatible

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.