


Input Controller 16

Input Controller 16



- **16 fully configurable inputs** One output 19 inch rack mount Standard equipped with Xlite Toolset, controlling software. Multipurpose device: both Daylight Display and Projection Arrange your sources onto your display through an intuitive interface. Scale and position all sources exactly how you want them. Overlay sources using advanced chroma-keying and alpha blending features. Process video and data in pure quality onto your display. Compatible with all standard image formats.

Технические характеристики

INPUT CONTROLLER 16

Общие характеристики

Ввод	16 user defined inputs Front accessible Integrated video processing Auto sensing, hot swappable S-video, composite, YUV, RGB SDI, HD-SDI, DVI up to UXGA
Совместимость	Barco Daylight Displays Projectors
Вывод	DVI-A, DVI-D, RGB
Контроль	· Scaler 16 input channels [Data-Video] fully scalable to desired output resolution · Z-order Instant modification of Z-order control, for each output window · Window positioning Intuitive positioning interface · Connectors RS 232 [RJ11]
Эффекты	Anamorphic imaging Chroma-keying [per input] Alpha-keying [per input] Z-order control Windowing/ View ports
Рабочая температура	0° <> 45°
Потребляемая энергия	240W-480W auto ranging 90-264V (50-60 Hz) Connector: 3 pin IEC
Информация о заказе	R9851580

Создано: 09 Jul 2024

© 2024 Барко нв. Все права защищены. Полное или частичное воспроизведение без письменного разрешения запрещено. Все названия брендов и продуктов являются товарными знаками, зарегистрированными товарными знаками или торговыми наименованиями соответствующих владельцев. В связи с непрерывными обновлениями информация и технические характеристики могут меняться без предварительного уведомления. Пожалуйста, проверьте www.barco.com для получения последних спецификаций.

www.barco.com

BARCO