

iD Pro R600

The smartest and brightest network centric single-chip DLP projector with SXGA+ resolution and an amazing brightness level of 6,000 ANSI lumens.



Product specificaties

ID PRO R600

General specifications

Lichtuitvoer	6,000 ANSI lumens
Resolutie	SXGA+ (1400 x 1050)
Helderheidsuniformiteit	> 95 % for the total screen
Contrastverhouding	2,000 : 1 (full white/full black)
Beeldscherm	1-chip 0.95" DarkChip3™ DLP™ SXGA+ panel, with a native resolution of 1400 x 1050 pixels, 4:3 aspect ratio
Kenmerken	■ AutoImage ■ Advanced picture-in-picture ■ Seamless switching with effects ■ Standard cable basket
Picture-in-Picture	Up to 3 sources simultaneously
Ingangen	■ 1x Component Video, RGBHV, RGBS or RGsB (5 BNC) ■ 1x Composite Video (BNC) ■ 1x S-Video (4-pin mini-DIN) ■ 1x VGA (D15 connector) ■ 1x DVI (Digital Visual Interface) ■ 1x SDI optional Audio connections: ■ 1x Stereo mic in ■ 1x Stereo line in ■ 1x Stereo line out
Uitgangen	No output
Communicatie	1x D9 connectors for RS232 In/Out 1x spherical IR receiver
Compatibiliteit	■ All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats ■ All currently proposed HDTV, extended and improved television standards (1080i, 720p) ■ All computer graphics formats from VGA, SVGA, XGA, SXGA to UXGA ■ Most Macintosh computers ■ Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz ■ Most computer sources with a pixel clock up to 160 MHz ■ DVI sources up to SXGA+
Compatibiliteit invoerbron	1600 x 1200 (max. input)
Schermaformaat	From 1-6m / 3-20ft.
Scanfrequenties	Horizontal 15kHz -110 kHz Vertical 25 Hz -150 Hz
Netwerkverbinding	1 x 10/100 Base-T Ethernet
Geïntegreerde beeldschermserver	Server Specifications: -Processor: Pentium M 1.6 GHz -Memory: 512 MB DDR RAM -Storage: 40 GB hard disk -Inputs and outputs: ■ PCMCIA slot for Wireless LAN cards, memory cards, Bluetooth, input extensions ... ■ RJ45connector for Ethernet (10Mb/s) and Fast Ethernet (100Mb/s) ■ 4 USB connectors ■ Audio: 3,5 mm jacks for Microphone in, Line in and Line out
Omgevingstemperatuur	5°C up to 40°C
Lamp	2 x 250 Watt UHP lamp, in lamp housing, pre-aligned for max. light output. Typical lifetime: 1,500 h/lamp. 1,500 hours in Dual Lamp Mode or 3,000 hours in Single Lamp Mode.
Lenzen	Fixed focal length lens with a throw ratio of 0.8:1 Variable focal length lenses with a throw distance of 1.1-1.3, 1.2-1.6, 1.6-2.4, 2.4-4.3 times the screen width
Lensverschuiving	Motorized V shift: -30% +110%
Lens-encoders	For specific details per lens type: see lens product pages
ScenergiX	Not Applicable
Verzegelde DLP™-kern	Not Applicable
Stoffilters	High Quality Microfilter (side removeable)
Geluidsniveau	< 41 dB
Netspanning	90V-255V
Energieverbruik	Max. 680 Watt
Vermogensdissipatie	Max. 2400 BTU/hour
Wisselstroom	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
Gewicht	Net weight: body only: 13.5 kg/29.8 lbs
Afmetingen	Projector body with cable basket: 415 mm (max. W) x 195 mm (max. H) x 565 (max. D) Projector body without cable basket: 415 mm(max. W) x 195 mm (max. H) x 487 (max. D)
Veiligheidsvoorschriften	Compliant with UL1950 and EN60950
Elektromagnetische storing	Compliant with FCC rules & regulations, part 15 Class B, CE EN55022 Class B and CCC

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.